




CoolSplice | CoolSplice Connectors

TE Internal #: 2213800-4

Splices, 22 – 20 AWG Wire Size, .34 – .52 mm<sup>2</sup> Wire Size, Sealable, Splice Capacity 4, End Feed, Phosphor Bronze, CoolSplice Connectors

[View on TE.com >](#)

Terminals & Splices > Splices > CoolSplice Quick Connect Splice



Wire Size: .34 – .52 mm<sup>2</sup>

Sealable: **Yes**

Splice Capacity: **4**

Splice Features: **End Feed**

[All CoolSplice Quick Connect Splice \(12\)](#)

**Features**

**Product Type Features**

Sealable	Yes
Splice Type	Butt Splice
Serrated	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Insulation Support

**Configuration Features**

Splice Capacity	4
Compatible With Wire & Cable Type	Discrete Wire

**Electrical Characteristics**

Operating Voltage	450V (IEC) / 600V (UL)
Current Rating	5 A

**Body Features**

Button Color	Blue
--------------	------



Splice Features	End Feed
-----------------	----------

Primary Product Material	Phosphor Bronze
--------------------------	-----------------

### Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

### Dimensions

Wire Size	.34 – .52 mm <sup>2</sup>
-----------	---------------------------

Accepts Wire Insulation Diameter Range	2.85 mm[.112 in]
--	------------------

Overall Product Length	36.4 mm[1.433 in]
------------------------	-------------------

### Usage Conditions

UV Exposure Rated	Yes
-------------------	-----

Insulation Option	Fully Insulated
-------------------	-----------------

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Heavy Duty	No
------------	----

Compatible With Wire Base Material	Copper
------------------------------------	--------

### Industry Standards

Agency/Standard	IEC, UL
-----------------	---------

UL Flammability Rating	UL 94V-2
------------------------	----------

Agency/Standard Number	IEC 60988-2-3, UL 1977, UL 2459
------------------------	---------------------------------

Government Qualified Splice	No
-----------------------------	----

### Packaging Features

Packaging Method	Box
------------------	-----

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content

Low Halogen - Br, Cl, F, I &lt; 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | CoolSplice Connectors



## Documents

## Product Drawings

COOLSPICE NEW STANDARD

English

## CAD Files

3D PDF

3D



**Customer View Model**

[ENG\\_CVM\\_CVM\\_2213800-4\\_D2.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2213800-4\\_D2.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2213800-4\\_D2.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Datasheets & Catalog Pages**

[CoolSplice New Standard flyer \(Chinese\)](#)

English

[CoolSplice Connector](#)

[CoolSplice Connector](#)

English

---

**Product Specifications**

[Application Specification](#)

English

---

**Product Environmental Compliance**

[Product Compliance](#)

English

[Product Compliance](#)

English

---

**Instruction Sheets**

[Instruction Sheet \(U.S.\)](#)

English

---

**Agency Approvals**

[DEKRA\\_CB\\_NL-68996\\_C1 CoolSplice IEC60998-2-3](#)

English