

2295205-1 ✓ ACTIVE




Dynamic Series | Dynamic Series Thermocouple Connector

TE Internal #: 2295205-1

PCB Connector Strain Relief, Strain Relief, Shield & Cable Clamp,
Stainless Steel, Wire-to-Board, Wire & Cable, Dynamic Series
Thermocouple Connector

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Connector Accessories > Protection & Strain Relief > PCB Connector Strain Relief



Protection & Strain Relief Accessory Type: **Strain Relief**

Strain Relief Type: **Shield & Cable Clamp**

Primary Product Material: **Stainless Steel**

Connector System: **Wire-to-Board**

Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Strain Relief
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Body Features

Strain Relief Type	Shield & Cable Clamp
Primary Product Material	Stainless Steel

Usage Conditions

Operating Temperature Range	-20 – 220 °C[-4 – 428 °F]
-----------------------------	---------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Dynamic Series Thermocouple Connector



Documents

[Product Drawings](#)



THERMOCOUPLE CONNECTOR.STRAIN RELIEF.

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2295205-1_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2295205-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2295205-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773895-2_THERMOCOUPLE_FLYER](#)

English

Product Specifications

[Product Specification](#)

Japanese

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English