



TE Internal #: 281871-3

Housing for Female Terminals, Wire-to-Wire, 2 Position, .196 in [5 mm] Centerline, Black, Wire & Cable, Signal, Cable Mount (Free-Hanging)

[View on TE.com >](#)

Connectors > Automotive Connectors > Connector Housings



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **5 mm [ .196 in ]**

Connector System: **Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **5 mm [ .196 in ]**

## Features

### Product Type Features

Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	No
Hybrid Connector	No
Primary Locking Feature	Integrated in Housing
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	2
Number of Rows	1

### Electrical Characteristics

Operating Voltage	24 VDC
Nominal Voltage Architecture	24 V

### Body Features

--	--



Cable Exit Angle	180°
Body Material	PA GF
Primary Product Color	Black
Connector Code	Neutral

#### Contact Features

Contact Size	5mm
Contact Type	Receptacle
Mating Tab Width	5 mm [.196 in]
Contact Current Rating (Max)	14 A

#### Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	No
Strain Relief	Without
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

#### Housing Features

Centerline (Pitch)	5 mm [.196 in]
--------------------	----------------

#### Dimensions

Product Width	11.8 mm [.465 in]
Product Length	16.3 mm [.648 in]
Product Height	22 mm [.866 in]

#### Usage Conditions

Operating Temperature (Max)	150 °C [302 °F]
Operating Temperature Range	-30 – 150 °C [-22 – 302 °F]

#### Operation/Application

Circuit Application	Signal
---------------------	--------

#### Packaging Features

Packaging Quantity	3000
Packaging Method	Box

#### Other

Serviceable	Yes
-------------	-----



Connector Position Assurance Capable No

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

<p>TE Part # 281866-3 5MM PITCH TAB/RECPT CONN</p>	<p>TE Part # 281869-1 5MM PITCH TAB/RECPT CONTA</p>	<p>TE Part # 281870-1 5MM PITCH TAB/RECPT CONTACT</p>
--	---	---

### Documents

[Product Drawings](#)  
5MM PITCH TAB/RECPT CONN



English

**CAD Files**

**Customer View Model**

[ENG\\_CVM\\_281871-3\\_B.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_281871-3\\_B.3d\\_stp.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_281871-3\\_B.2d\\_dxf.zip](#)

English

**3D PDF**

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Product Specifications**

**Terminale femmina adatto per correnti fino a 20A**

English

**Product Specification**

English

**terminale femmina adatto per correnti fino a 15A**

English

**Product Specification**

English

**connettore passo 5mm. con arpionismo a scatto**

English

**Product Specification**

English