



Cable Assemblies > Copper Cable Assemblies > Lighting Cable Assemblies



Wire Color (Base): **Green**

Voltage Rating: **600 VAC**

Number of Positions: **1**

Operating Temperature Range: **-40 – 105 °C**

### Features

#### Product Type Features

Wire/Cable Type	Discrete Wire
Applies To	Wire/Cable
Cable Assembly System	Wire-to-Wire

#### Configuration Features

Number of Positions	1
---------------------	---

#### Electrical Characteristics

Operating Voltage	600 V
Operating Voltage Reference	AC
Voltage Rating	600 VAC

#### Body Features

Wire Color (Base)	Green
-------------------	-------

#### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

#### Dimensions

Wire Size	18 AWG
-----------	--------

#### Usage Conditions

Operating Temperature Range	-40 – 105 °C
-----------------------------	--------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Documents

### Product Drawings

[CABLE ASSEMBLY, GROUND CLIP 4 INCHES](#)

English



---

[Datasheets & Catalog Pages](#)

[Ground Clip Assembly \(Chinese\)](#)

English

[1-1773919-9\\_Ground\\_Clip\\_Assembly](#)

English