

293387-1 ✓ ACTIVE

NECTOR | NECTOR S

TE Internal #: 293387-1

Plug & Socket Lighting Connector Accessories, Wire-to-Wire, 2 Position, .141 in [3.6 mm] Centerline, Wire & Cable, 125 VAC, Power, NECTOR S

[View on TE.com >](#)



Connectors > Lighting Connectors > Plug & Socket Connector Accessories



Connector System: **Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **3.6 mm [.141 in]**

Connector & Contact Terminates To: **Wire & Cable**

Operating Voltage: **125 VAC**

Features

Product Type Features

Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
---------------------	---

Electrical Characteristics

Operating Voltage	125 VAC
-------------------	---------

Contact Features

Contact Current Rating (Max)	6 A
------------------------------	-----

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	3.6 mm[.141 in]
--------------------	-----------------

Operation/Application

Circuit Application

Power

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)
Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | **NECTOR S**




Insertion & Extraction Tools(3)



Lighting Cable Assemblies(1)



Plug & Socket Lighting Connector Accessories(57)



Plug & Socket Lighting Connectors(54)

Documents

Product Drawings

NECTOR S OUTLET HV-3 WHITE

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_293387-1_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_293387-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_293387-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

NECTOR_S_LINE_CONNECTOR_BROCHURE

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL Report

English