



**NECTOR | NECTOR S**

TE Internal #: 293387-3

Plug & Socket Lighting Connector Accessories, Wire-to-Wire, 2 Position, .141 in [3.6 mm] Centerline, Wire & Cable, 125 VAC, Power, NECTOR S

[View on TE.com >](#)

Connectors > Lighting Connectors > Plug & Socket Connector Accessories



Connector System: **Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **3.6 mm [ .141 in ]**

Connector & Contact Terminates To: **Wire & Cable**

Operating Voltage: **125 VAC**

**Features**

**Product Type Features**

Connector System	Wire-to-Wire
Connector & Contact Terminates To	Wire & Cable

**Configuration Features**

Number of Positions	2
---------------------	---

**Electrical Characteristics**

Operating Voltage	125 VAC
-------------------	---------

**Contact Features**

Contact Current Rating (Max)	6 A
------------------------------	-----

**Mechanical Attachment**

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

**Housing Features**

Centerline (Pitch)	3.6 mm[.141 in]
--------------------	-----------------

**Operation/Application**



Circuit Application	Power
---------------------	-------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



Also in the Series | **NECTOR S**



Insertion &amp; Extraction Tools(3)



Lighting Cable Assemblies(1)



Plug &amp; Socket Lighting Connector Accessories(57)



Plug &amp; Socket Lighting Connectors(54)

## Documents

### Product Drawings

#### NECTOR S OUTLET HV-4 WHITE

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_293387-3\\_C.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_293387-3\\_C.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_293387-3\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### NECTOR\_S\_LINE\_CONNECTOR\_BROCHURE

English

### Agency Approvals

#### UL Report

English