




Agastat 7000

TE Internal #: 2-1768040-1

Pre-Printed Markers, Snap-On, Red, Straight Cut, A Printed Marking, Width 5.5 mm [.216 in], White, Thermoplastic, Agastat 7000

[View on TE.com >](#)

Identification & Labeling > Pre-Printed Markers > STD Snap-On Markers



Marker Style: **Snap-On**

Compatible Cable Diameter Range: **8.5 – 11.5 mm [.335 – .452 in]**

Primary Product Color: **Red**

Marker Cut: **Straight**

Printed Marking: **A**

[All STD Snap-On Markers \(966\)](#)

Features

Body Features

Marker Style	Snap-On
Primary Product Color	Red
Primary Product Material	Thermoplastic

Dimensions

Compatible Cable Diameter Range	8.5 – 11.5 mm [.335 – .452 in]
Product Width	5.5 mm [.216 in]

Printer/Label Features

Marker Cut	Straight
Printed Marking	A

Other

Printed Marking Color	White
-----------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | [Agastat 7000](#)



Pre-Printed Markers(963)



Time Delay Relays(176)

Documents

Product Drawings

[STB17-A-2](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-1768040-1_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1768040-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1768040-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[STD and STB Technical Datasheet](#)

English