



SL-156

TE Internal #: 2-640251-2

Housing, Receptacle, Wire-to-Board, 22 Position, 3.96 mm [.156 in]
Centerline, Crimp, 1 Row, Natural, Wire & Cable, Power & Signal,
SL-156

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings >

Receptacle Housing: Wire-to-Board, no Mating Alignment, SL 156



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **22**

Centerline (Pitch): **3.96 mm [.156 in]**

[All Receptacle Housing: Wire-to-Board, no Mating Alignment, SL 156 \(30\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	22
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

--	--



Contact Layout	Inline
Contact Retention Within Housing	Without
Contact Type	Socket
Contact Current Rating (Max)	6.5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Entry Configuration	Left End Open
Housing Material	Nylon - GF
Centerline (Pitch)	3.96 mm [.156 in]
Housing Color	Natural

Dimensions

	3.433 in
Connector Height	6.35 mm
Wire Size	.0509 – .823 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

CSA Rating	Certified
UL Flammability Rating	UL 94V-0
UL File Number	E28476
UL Rating	Listed
Agency/Standard	CSA, UL



CSA File Number	LR 7189
-----------------	---------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Other

Comment	Unit Accepts 1.14[.045] Square or Round Post, Accepts Keying Plug 640254-1 and 640255-1
---------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CAT-103156-WBHSN
Receptacle Housing: Wire-to-Board, no Mating Alignment, SL 156



TE Part # 2-640445-2
22P MTA156 HDR ASSY FL/STR SN



TE Part # 2-643067-2
22P MTA156 MOLDED COVER



TE Part # 2-640383-2
22P MTA156 HDR ASSY STR SQ SN



TE Part # 2-640385-2
22P MTA156 HDR ASSY SQ R/A



TE Part # 2-640387-2
22P MTA156 HDR ASSY SQ R/A



TE Part # 2-640388-2
22P MTA156 HDR ASSY RN STR F/L



TE Part # 2-640389-2
22P MTA156 HDR ASSY SQ R/A F/L



TE Part # 2-640551-2
22P MTA156 COVER



TE Part # 2-640643-2
22P MTA156 COVER F/T



TE Part # 2-643071-2
22P MTA156 FD-THRU COVER



TE Part # 2-644749-2
22P MTA156 HDR ASSY STR SQ SN



TE Part # 2-644750-2
22P MTA156 HDR ASSY STR RND SN



TE Part # 2-644751-2
22P MTA156 HDR ASSY R/A



TE Part # 2-644752-2
22P MTA156 HDR ASSY SQ STR F/L



TE Part # 2-644753-2
22P MTA156 HDR ASSY RN STR F/L



TE Part # 5-641113-2
22P MTA156 HDR ASSY 15AU LF



TE Part # 5-641119-2
22P MTA156 HDR ASSY FL/ST LF



TE Part # 5-641120-2
22P MTA156 HDR ASSY FL/ST LF



TE Part # 5-641121-2
22P MTA156 HDR ASSY FL/RA LF


Also in the Series | [SL-156](#)



Insertion & Extraction Tools(1)



PCB Connector Keying(2)



PCB Latches, Locks & Retainers(1)



Rectangular Connector Housings(12)



Rectangular Connector Keying Plugs(1)



Wire-to-Board Connector Assemblies & Housings(158)



Wire-to-Board Connector Contacts(24)

Documents

Product Drawings

22P SL156 HSG W/O LCK RAMP

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-640251-2_AL_c-2-640251-2-al.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-640251-2_AL_c-2-640251-2-al.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-640251-2_AL_c-2-640251-2-al.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MTA, CST-100 II, SL-156 and AMP Economy Power (EP) Connectors

English

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

2-640251-2

Housing, Receptacle, Wire-to-Board, 22 Position, 3.96 mm [.156 in] Centerline, Crimp,
1 Row, Natural, Wire & Cable, Power & Signal, SL-156



English