




SOLISTRAND

TE Internal #: 34137-4

Splices, 16 – 14 AWG Wire Size, 1.25 – 2 mm² Wire Size, .085 in [2.15 mm] Barrel Inside Diameter, 2.05 – 5.18 kcmil Wire Size

[View on TE.com >](#)

Terminals & Splices > Splices



Wire Size: 2.05 – 5.18 kcmil

Sealable: No

Barrel Inside Diameter: 2.15 mm [.085 in]

Features

Product Type Features

Discrete Wire Type	Solid or Stranded
Splice Accessory Type	Splice
Sealable	No
Splice Type	Parallel Splice
Serrated	Yes
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

	100 μin
Plating Material	Gold
Primary Product Material	Copper

Contact Features

	100 μin
Contact Plating Material	Gold



Barrel Type	Closed
-------------	--------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

	.165 in
Wire Size	2050 – 5180 CMA
Barrel Inside Diameter	2.15 mm[.085 in]
Terminal Material Thickness	.84 mm[.033 in]
Overall Product Length	7.64 mm[.301 in]

Usage Conditions

High Temperature Rating	260 °C[500 °F]
Insulation Option	Uninsulated
Operating Temperature Range	260 °C[500 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece

Other

Military Category	No
-------------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Documents

Product Drawings

SOLI,PSP,16-14,AU

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_34137-4_P.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_34137-4_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_34137-4_P.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOLISTRAND - QRG](#)

English