



**AMPOWER**

TE Internal #: 325906-3

Ring Terminals & Spade Terminals, Rectangular Tongue, 325000 – 375000 CMA Wire Size, Tongue Thickness 4.32 mm [.17 in], Closed, Straight, AMPOWER

[View on TE.com >](#)

Terminals & Splices > Ring Terminals & Spade Terminals > AMPOWER TERMINAL 2 STUD HOLES



Ring & Spade Terminal Type: **Rectangular Tongue**

Wire Size: **325000 – 375000 CMA**

Tongue Thickness: **4.32 mm [.17 in]**

Barrel Type: **Closed**

Terminal Orientation: **Straight**

[All AMPOWER TERMINAL 2 STUD HOLES \(25\)](#)

**Features**

**Product Type Features**

Sealable	No
----------	----

**Configuration Features**

Terminal Angle	180 °
----------------	-------

**Body Features**

Inspection Slot	Yes
Weight per Piece	93.894 g

**Contact Features**

Ring & Spade Terminal Type	Rectangular Tongue
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Unplated

**Mechanical Attachment**



Wire Insulation Support	Without
-------------------------	---------

### Dimensions

Wire Size	325000 – 375000 CMA
Tongue Thickness	4.32 mm [.17 in]
Overall Product Length	73.91 mm [2.91 in]
Barrel Inside Diameter	20.8 mm [.819 in]

### Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]

### Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin
Heavy Duty	No

### Industry Standards

Government Qualified	No
----------------------	----

### Packaging Features

Packaging Quantity	25
Packaging Method	Box

### Other

Comment	Cleaned but not plated.
---------	-------------------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts




TE Part # 46753-2  
HYP8 AMPOWER 350MCM DIE SET




TE Part # 69653  
HYP8 AMPOWER 350MCM 69082 DIE SET

### Also in the Series | AMPOWER




Busbar Connectors(13)




Knife Disconnects(15)




PCB Headers & Receptacles(2)



Power Cable Assemblies(7)




Power Contacts(1)



Quick Disconnects(1)



Rectangular Power Connectors(6)



Ring Terminals & Spade Terminals(141)



Splices(40)

## Documents

### Product Drawings

[TERM,AMPOWER 350MCM 0 UNPLTD](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_325906-3\\_AE.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_325906-3\\_AE.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_325906-3\\_AE.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[AMPOWER Terminals and Splices Flyer](#)

English