

42076 ✓ ACTIVE

AMPLIVAR


TE Internal #: 42076

Splices, 22 – 15 AWG Wire Size, .3 – 1.5 mm² Wire Size, Splice Capacity 3, End Feed, .065 in [1.66 mm] Barrel Inside Diameter, AMPLIVAR

[View on TE.com >](#)



Terminals & Splices > Splices



Wire Size: .3 – 1.5 mm²

Sealable: No

Splice Capacity: 3

Splice Features: End Feed

Features

Product Type Features

Sealable	No
Splice Type	Thru Splice
Serrated	Yes
Compatible With Discrete Wire Type	Magnet Wire, Solid

Configuration Features

Strip Orientation	End Feed
Splice Capacity	3
Number of Serrations	5

Electrical Characteristics

Operating Voltage	250 V
-------------------	-------

Body Features

Weight per Piece	.19 g
Plating Material	Unplated
Splice Features	End Feed



Primary Product Material	Brass
--------------------------	-------

Contact Features

Contact Plating Material	Unplated
--------------------------	----------

Barrel Type	Open
-------------	------

Termination Features

Crimp Width	2.79 mm [.11 in]
-------------	------------------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	600 – 3000 CMA
-----------	----------------

Barrel Inside Diameter	1.66 mm [.065 in]
------------------------	-------------------

Terminal Material Thickness	.51 mm [.02 in]
-----------------------------	-----------------

Overall Product Length	5.72 mm [.225 in]
------------------------	-------------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operating Temperature Range	-65 – 150 °C [-85 – 302 °F]
-----------------------------	-----------------------------

Operation/Application

Heavy Duty	No
------------	----

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	30000
--------------------	-------

Packaging Method	Strip
------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224)
--	--









Candidate List Declared Against: JUNE 2022 (224)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 63564-1 SPLICE AMVAR 2000-5400 020BR</p>	 <p>TE Part # 42192-1 SPLC AMVAR 600-3000 020BR</p>	 <p>TE Part # 1217384-1 AMVAR SPL 600-3000 7 SERR TPBR</p>	 <p>TE Part # 170152-3 AMP SPLICE</p>
 <p>TE Part # 42192-2 SPLC AMVAR 600-3000 020TPBR</p>	 <p>TE Part # 566398-1 EF THRU SPLICE APPL 110F</p>		

Also in the Series | **AMPLIVAR**




Crimp Wire Pins, Tabs & Ferrules(5)



Magnet Wire Terminals(5)



PCB Terminals(1)



Quick Disconnects(42)



Ring Terminals & Spade Terminals(28)



Splices(78)

Documents

Product Drawings

[SPLC AMVAR 600-3000 020BR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_42076_BC_c-42076-bc.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_42076_BC_c-42076-bc.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_42076_BC_c-42076-bc.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

[Magnet Wire Terminals & Splices](#)

English

Product Specifications

[Application Specification](#)

English



AMPLIVAR 5 Serration Thru Splice

English

No title

Japanese

Application Specification

Japanese

No title

English

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English