

499252-3 ✓ ACTIVE

## AMP-LATCH

TE Internal #: 499252-3

TE Internal Description: 026 STRAIN RELIEF A-L RCPT


Bus Connector: Strain Relief, ATA

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Connector Accessories >

Bus Connector: Strain Relief, ATA



Flat Flexible Cable Accessory Type: **Strain Relief**

[All Bus Connector: Strain Relief, ATA \(13\)](#)

## Features

### Product Type Features

Flat Flexible Cable Accessory Type	Strain Relief
------------------------------------	---------------

### Body Features

Primary Product Material	Thermoplastic
--------------------------	---------------

Primary Product Color	Black
-----------------------	-------

### Dimensions

Product Width	6.1 mm[.24 in]
---------------	----------------

Product Length	37.85 mm[1.49 in]
----------------	-------------------

Product Height	14.76 mm[.581 in]
----------------	-------------------

### Industry Standards

CSA File Number	LR 7189
-----------------	---------

Agency/Standard	CSA, UL
-----------------	---------

UL Rating	Recognized
-----------	------------

UL File Number	E28476
----------------	--------

### Packaging Features

Packaging Quantity	500
--------------------	-----



Packaging Method

Box & Carton

Other

Comment

Receptacle Connector

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)  
Candidate List Declared Against: JUNE 2022 (224)  
Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-AM74-UN384H  
AMP-LATCH UNIVERSAL HEADERS



TE Part # 2-111506-1  
026 UNIV I/O 30DP SLOT LTCH



TE Part # 2-1761607-9  
IDC LOW PRO HDR 26P RA LG LAT



TE Part # 1658622-6  
26 NOVO MIL/CTR 30DP, LEAD FREE



## Documents

### Product Drawings

026 STRAIN RELIEF A-L RCPT

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_499252-3\\_AL.2d\\_dxf.zip](#)

English

[3D PDF](#)

[3D](#)



**Customer View Model**

[ENG\\_CVM\\_CVM\\_499252-3\\_AL.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_499252-3\\_AL.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Datasheets & Catalog Pages**

[Ribbon Cable Interconnect Solutions](#)

English

---

**Product Specifications**

[Application Specification](#)

English

---

**Product Environmental Compliance**

[MD\\_499252-3\\_04232018047\\_dmtec](#)

English

[MD\\_499252-3\\_04232018047\\_dmtec](#)

English