



AMP

TE Internal #: 539691-2

Hand Crimping Tools, Commercial Crimp Tooling, Operator Releasable & Adjustable, Removable/Interchangeable, TE Product Specification (114-), Manual

[View on TE.com >](#)

Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**

Ratchet Configuration: **Operator Releasable & Adjustable**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Upon Request for Fee**

**Features**

**Other**

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Manual
Tooling Type	Ergocrimp Hand Tool Assembly or Die

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (.35% in Component Part)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-P592-R472A  
PIDG RING TONGUE TERMINALS



TE Part # CAT-P592-SP118  
PIDG Spade Tongue Terminals



TE Part # CAT-P592-F614  
PIDG Flanged Spade Tongue Terminals



TE Part # CAT-P592-SH816  
PIDG Short Spring Spade Tongue Terminals



TE Part # CAT-P592-K742  
PIDG Knife Disconnect Splices



TE Part # CAT-P592-ST433  
PIDG Stepdown Butt Splices



TE Part # CAT-P592-F266  
PIDG FASTON Receptacle Quick Disconnects



TE Part # CAT-P592-L853  
PIDG Long Spring Spade Tongue Terminals



TE Part # 160834-2  
PIDG PIGGY-B FASTON



TE Part # CAT-P592-F766  
PIDG Formed Wire Pins



TE Part # CAT-P592-SL56  
PIDG Slotted Ring Tongue Terminals



TE Part # CAT-P592-R2456  
PIDG Rectangular Tongue Terminals



## Documents

### Product Drawings

#### ERGO DIE R.B.Y

German

### Datasheets & Catalog Pages

#### 1-1773865-2\_1015\_Commercial Manual Hand Tools

English

### Bottoming Dies

English

### Instruction Sheets

#### Instruction Sheet (non U.S.)

German