

54012-4 ✓ ACTIVE

AMP | AMP CPC


TE Internal #: 54012-4

Circular Connector Seals, Cable Seal, Cable-to-Cable, 1-7/16-18, Sealable, Wire & Cable, Cable Mount (Free-Hanging), AMP CPC

[View on TE.com >](#)



[Connectors](#) > [Circular Connectors](#) > [Circular Connector Accessories](#) > [Circular Connector Seals](#) > [CPC Heat Shrink Strain Reliefs](#)



Connector Seal Type: **Cable Seal**

Connector System: **Cable-to-Cable**

Accepts Cable Diameter Range: **13.97 – 31.75 mm [.55 – 1.25 in]**

Screw & Hole Thread Size: **1-7/16-18**

Sealable: **Yes**

[All CPC Heat Shrink Strain Reliefs \(7\)](#)

Features

Product Type Features

Connector Seal Type	Cable Seal
Connector System	Cable-to-Cable
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Body Features

Color	Black
-------	-------

Mechanical Attachment

Screw & Hole Thread Size	1-7/16-18
Connector Mounting Type	Cable Mount (Free-Hanging)

Dimensions

Accepts Cable Diameter Range	13.97 – 31.75 mm [.55 – 1.25 in]
------------------------------	----------------------------------

Usage Conditions

Operating Temperature Range	-55 – 110 °C [-67 – 230 °F]
-----------------------------	-----------------------------

Packaging Features

Packaging Quantity	50
Packaging Method	Carton



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer












This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # CAT-AM71-C83998C Circular Plastic Connector, CMC Series 1</p>	 <p>TE Part # CAT-AM71-C83998S Circular Plastic Connector with Metal Shell, CMC Series 4</p>	 <p>TE Part # CAT-AM71-C83998R Circular Connector, CMC Series 3</p>	 <p>TE Part # 1776089-1 CMC PLUG ASSEMBLY, SZ 28</p>
--	---	--	---



Also in the Series | AMP CPC



Documents

[Product Drawings](#)
[CPC STRAIN RELIEF,SIZE 23](#)

English

[CAD Files](#)
[3D PDF](#)
3D
[Customer View Model](#)



[ENG_CVM_CVM_54012-4_Y.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_54012-4_Y.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_54012-4_Y.3d_stp.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_54012-4_V.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_54012-4_V.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_54012-4_V.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP Circular Connectors for Commercial Signal & Power Applications Continued](#)

English

Agency Approvals

[CSA Certificate](#)

English