




CII | CII FCA-125 Series

TE Internal #: 5-1617748-8

Mid-Range Relays, 1 Form C, SPDT, 1 C/O, Tin-Lead Terminal Plating, 25 A, 28 VDC Coil Voltage, 320 Ω Coil Resistance, CII FCA-125 Series

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Mil-Aero Relays > Mid-Range Relays



Mid-Range Relay Contact Arrangement: **1 Form C, SPDT, 1 C/O**

Coil Suppression Diode: **Without**

Auxiliary Contacts: **Without**

Terminal Plating: **Tin-Lead**

Mid-Range Relay Contact Current Rating: **25 A**

**Features**

**Product Type Features**

|                        |                              |
|------------------------|------------------------------|
| Enclosure Type         | Hermetically Sealed          |
| Terminal Configuration | Solder Hook                  |
| Product Type           | Relay                        |
| Relay Type             | Military/Aerospace Mid-Range |

**Electrical Characteristics**

|                                     |                       |
|-------------------------------------|-----------------------|
| Vibration                           | 30G's, 10 – 3000Hz    |
| Shock                               | 200G's, 6ms           |
| Coil Suppression Diode              | Without               |
| Mid-Range Relay Coil Voltage Rating | 28 VDC                |
| Mid-Range Relay Coil Resistance     | 320 Ω                 |
| Back EMF Suppression                | Without               |
| Coil Magnetic System                | Polarized, Monostable |
| Actuating System                    | DC                    |

**Signal Characteristics**

|           |        |
|-----------|--------|
| Frequency | 400 Hz |
|-----------|--------|

**Contact Features**

|                                     |                       |
|-------------------------------------|-----------------------|
| Mid-Range Relay Contact Arrangement | 1 Form C, SPDT, 1 C/O |
| Auxiliary Contacts                  | Without               |



|  |                      |
|--|----------------------|
| Terminal Plating                       | Tin-Lead             |
| Mid-Range Relay Contact Current Rating | 25 A                 |
| Contact Base Material                  | Silver Cadmium Oxide |

### Mechanical Attachment

|                               |                         |
|-------------------------------|-------------------------|
| Mid-Range Relay Mounting Type | Horizontal Flange Mount |
|-------------------------------|-------------------------|

### Usage Conditions

|                             |              |
|-----------------------------|--------------|
| Operating Temperature Range | -70 – 125 °C |
|-----------------------------|--------------|

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |  |
|---|--|
| EU RoHS Directive 2011/65/EU                  | Not Compliant  |
| EU ELV Directive 2000/53/EC                   | Not Compliant  |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2022 (224)<br>Candidate List Declared Against: JAN 2022 (223)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free  |
| Solder Process Capability                     | Not lead free process capable  |


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | CII FCA-125 Series



### Documents

#### Product Drawings

[FCA-125-9=M6106/19-009](#)

English

#### Datasheets & Catalog Pages

[5-1773450-5\\_sec5\\_FCA-125](#)

English

[RELAY](#)

English