

533236-7 ✓ ACTIVE

## EUROCARD

TE Internal #: 533236-7

PCB Connector Shrouds, Shroud, Mating Alignment, 96 Position, 2.54 mm [.1 in] Centerline, 3 Row, 32 Column, Length 3.47 in [88.14 mm]

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Connector Accessories > Protection & Strain Relief > PCB Connector Shrouds



Connector Mounting Accessory Type: **Shroud**

Standoff Height: **3.43 mm [.135 in]**

Mating Alignment: **With**

Number of Positions: **96**

Centerline (Pitch): **2.54 mm [.1 in]**

### Features

#### Product Type Features

Connector Mounting Accessory Type	Shroud
Sealable	No

#### Configuration Features

Number of Positions	96
Number of Rows	3
Number of Columns	32

#### Body Features

Shroud Material	Glass Filled Polyester
Shroud Color	Gray

#### Contact Features

CompactPCI	No
------------	----

#### Mechanical Attachment

Mating Alignment Type	Polarization
-----------------------	--------------



PCB Mount Retention	Without
---------------------	---------

Mating Alignment	With
------------------	------

### Housing Features

Centerline (Pitch)	2.54 mm [.1 in]
--------------------	-----------------

### Dimensions

PCB Thickness (Recommended)	2.36 mm [.093 in]
-----------------------------	-------------------

Standoff Height	3.43 mm [.135 in]
-----------------	-------------------

Row-to-Row Spacing	2.54 mm [.1 in]
--------------------	-----------------

Product Length	88.14 mm [3.47 in]
----------------	--------------------

Product Height	12.32 mm [.485 in]
----------------	--------------------

Product Width	11.1 mm [.437 in]
---------------	-------------------

### Usage Conditions

Compatible With Backplane Connector Type	Type C, Type R
------------------------------------------	----------------

Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]
-----------------------------	-----------------------------

### Operation/Application

Solder Process Feature	Board Standoff
------------------------	----------------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Method	Carton
------------------	--------

### Other

Comment	Shrouds are for use with all 48 & 96 position, 3 row, Type C and R connectors mounted in 3.18 [.125], 2.36 [.093], and 1.57 [.062] thick PC boards. Twelve interference areas are located in selected cavities.
---------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
-----------------------------------------------	-----------------------------------------

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224)
----------------------------------------	----------------------------------------------



Candidate List Declared Against: JUNE  
2022 (224)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Documents

### Product Drawings

#### 096 EURO SHROUD

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_533236-7\\_W.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_533236-7\\_W.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_533236-7\\_W.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Application Specification

English

### Product Environmental Compliance

#### TE Material Declaration

English

533236-7

PCB Connector Shrouds, Shroud, Mating Alignment, 96 Position, 2.54 mm [.1 in]  
Centerline, 3 Row, 32 Column, Length 3.47 in [88.14 mm]

