




Terminals &amp; Splices &gt; Ring Terminals &amp; Spade Terminals

Ring & Spade Terminal Type: **Ring Tongue**Wire Size: **254 – 1021 CMA**Stud Size: **#6, M3.5**

## Features

### Product Type Features

Shape Description	Flat Sided
Stud Size	#6, M3.5
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

### Configuration Features

Number of Holes	1
Terminal Angle	180 °

### Contact Features

Contact Base Material	Brass
Ring & Spade Terminal Type	Ring Tongue
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	Nickel

### Mechanical Attachment



Wire Insulation Support	With
-------------------------	------

### Dimensions

	.048 in
Wire Size	254 – 1021 CMA
Stud Diameter	3.6 mm[.142 in]
Tongue Thickness	.51 mm[.02 in]
Overall Product Length	14.22 mm[.56 in]
Barrel Inside Diameter	1.01 mm, 1.77 mm[.04 in][.07 in]
Accepts Wire Insulation Diameter (Max)	1.98 mm[.078 in]
Accepts Wire Insulation Diameter Range	1.22 – 1.98 mm[.048 – .078 in]

### Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

### Operation/Application

Compatible With Wire Base Material	Copper
Heavy Duty	No

### Industry Standards

Government Qualified	No
----------------------	----

### Packaging Features

Packaging Quantity	12000
Packaging Method	Strip/Reel

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Documents

## Product Drawings

RING 160 CRIMP TAB 26-20 AWG TPBR

English

## CAD Files

3D PDF

3D

## Customer View Model

ENG\_CVM\_CVM\_60123-2\_AH\_c-60123-2-ah.2d\_dxf.zip

English



### Customer View Model

[ENG\\_CVM\\_CVM\\_60123-2\\_AH\\_c-60123-2-ah.3d\\_igs.zip](#)

English

### Customer View Model

[ENG\\_CVM\\_CVM\\_60123-2\\_AH\\_c-60123-2-ah.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

[Engineering Report](#)

English

### Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English