

60385-2 ✓ ACTIVE

## AMPLIVAR


TE Internal #: 60385-2

Quick Disconnects, Receptacle, 18 – 14 AWG Wire Size, .82 – 2.08 mm<sup>2</sup> Wire Size, 2000 – 4500 CMA Wire Size, Mating Tab Width .25 in [6.35 mm], AMPLIVAR

[View on TE.com >](#)



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **2000 – 4500 CMA**

Mating Tab Width: **6.35 mm [ .25 in ]**

### Features

#### Product Type Features

Terminates To	Wire & Cable
Wire/Cable Type	Magnet Wire
Insertion Force	Low

#### Configuration Features

Connection Capacity	Single
---------------------	--------

#### Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm [.25 in]
Mating Tab Thickness	.81 mm [.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

#### Mechanical Attachment



Mating Retention Type	Dimple
-----------------------	--------

Wire Insulation Support	Without
-------------------------	---------

### Dimensions

Accepts Wire Insulation Diameter Range	3.1 – 4.3 mm [.12 – .17 in]
--	-----------------------------

Overall Length	17.53 mm [.69 in]
----------------	-------------------

Receptacle Terminal Stock Thickness	.4 mm [.016 in]
-------------------------------------	-----------------

Wire Size	2000 – 4500 CMA
-----------	-----------------

### Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

### Industry Standards

UL Rating	Listed
-----------	--------

CSA Certified	Yes
---------------	-----

### Packaging Features

Packaging Quantity	12000
--------------------	-------

Packaging Method	Reel
------------------	------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 62080-1 250 FAST RCPT 1000-3000 BR</p>	 <p>TE Part # 63622-1 RCPT AMVAR 250 FAST LIF 016BR</p>	 <p>TE Part # 63497-1 AMPLIVAR TAB 032 TPBR</p>	 <p>TE Part # 63165-1 250 AMVAR FAST TAB 032TPBR</p>
 <p>TE Part # 60384-2 .250 FAST REC IS 1000 TPBR</p>	 <p>TE Part # 1742944-1 RCPT 250 FLG FAST AMVAR TPPHBZ</p>	 <p>TE Part # 60177-2 .090 PIN REC AMVAR 21-16 TPPHB</p>	 <p>TE Part # 62922-1 250 FAST TAB AMVAR 032TPBR</p>
 <p>TE Part # 1217624-1 .187 FAST FL AMVR 0157 TPBR</p>	 <p>TE Part # 1217835-1 RECP AMVAR 250 FAST 016BR</p>	 <p>TE Part # 2232995-1 187 RCPT FAST AMVR 0157TPPB</p>	 <p>TE Part # 60384-1 .250 FAST REC IS 1000 BR</p>
 <p>TE Part # 62069-1 250 AMVAR FAS REC 23 19 MAG BR</p>	 <p>TE Part # 62091-2 250 FLG FAST RCPT 18-12 PTPBR</p>	 <p>TE Part # 63349-1 250 F TAB AMVAR 18-14 032TPBR</p>	 <p>TE Part # 63497-2 AMPLIVAR TAB 032 TPBR</p>



## Also in the Series | AMPLIVAR



## Documents

### Product Drawings

[.250 FAST REC IS 18-2/17 TPBR](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_60385-2\\_AB.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_60385-2\\_AB.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_60385-2\\_AB.3d\\_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[82004 FASTON Terminals \(Insulated and Uninsulated\) Catalog - FASTON Receptacles Section](#)

English

---

### Product Specifications

[Application Specification](#)

English

---

### Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

---

### Agency Approvals

[CSA Certificate](#)

English

[CSA Certificate](#)

English