


**SPLICE**

TE Internal #: 60932-2

Splices, 2500 – 4700 CMA Wire Size, Steel, Pigtail Splice / Thru Splice Splice, 0 Serration, Length 5.56 mm [.219 in], Reel, Open, SPLICE

[View on TE.com >](#)

Terminals &amp; Splices &gt; Splices

Sealable: **No**Wire Size: **2500 – 4700 CMA**Primary Product Material: **Steel**Splice Type: **Pigtail Splice, Thru Splice**Terminal Material Thickness: **.5 mm [.02 in]****Features****Product Type Features**

Barrel Style	Standard
Sealable	No
Splice Type	Pigtail Splice, Thru Splice
Serrated	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

**Configuration Features**

Number of Serrations	0
Compatible With Wire & Cable Type	Discrete Wire

**Body Features**

Weight per Piece	.149 g
Plating Material	Tin
Primary Product Material	Steel

**Contact Features**



Barrel Type	Open
-------------	------

### Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

### Dimensions

Wire Size	2500 – 4700 CMA
-----------	-----------------

Terminal Material Thickness	.5 mm[.02 in]
-----------------------------	---------------

Overall Product Length	5.56 mm[.219 in]
------------------------	------------------

### Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]
-----------------------------	----------------------------

### Operation/Application

Heavy Duty	No
------------	----

Compatible With Wire Base Material	Copper
------------------------------------	--------

### Industry Standards

Government Qualified Splice	No
-----------------------------	----

### Packaging Features

Packaging Quantity	50000
--------------------	-------

Packaging Method	Reel
------------------	------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---















Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 61300-1 SPLICE IS 10000-16000 .031 TPST</p>	 <p>TE Part # 42627-4 SPLICE 3232-8282 .0198 NPST</p>	 <p>TE Part # 63414-1 SPLICE 9000-16000 .031 TPST</p>	 <p>TE Part # 60933-2 SPLICE 2200-2900 .012 TPST</p>
 <p>TE Part # 41627-1 SPLICE 4000-10000 .025 ST</p>	 <p>TE Part # 61008-1 SPLICE 18-16 AWG .0158 TPST</p>	 <p>TE Part # 160659-2 SPLICE 800-2500 .016 NPST</p>	 <p>TE Part # 2-2150102-1 OCEAN_2.0_Applicator-E-120F</p>
 <p>TE Part # 2-2150102-2 OCEAN_2.0_Applicator-E-120F</p>	 <p>TE Part # 2150102-1 OCEAN_2.0_Applicator-E-120F</p>	 <p>TE Part # 2150102-2 OCEAN_2.0_Applicator-E-120F</p>	 <p>TE Part # 7-2150102-1 OCEAN_2.0_Applicator-E-120F</p>
 <p>TE Part # 7-2150102-2 OCEAN_2.0_Applicator-E-120F</p>	 <p><b>KIT</b> REPRESENTATION ONLY</p> <p>TE Part # 7-2150102-7 OCEAN_2.0_SPARE_PART_KIT-120F</p>		

## Also in the Series | SPLICE



Crimp Wire Pins, Tabs & Ferrules(1)



Splices(65)

## Documents

### Product Drawings

[SPLICE 2500-4700 .020 TPST](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_60932-2\\_S.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_60932-2\\_S.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_60932-2\\_S.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

[Application Specification](#)

English

### Product Environmental Compliance

[TE Material Declaration](#)

English