

61365-1 ✓ ACTIVE

FASTON | FASTON 250


TE Internal #: 61365-1

PCB Terminals, Tab, Mating Tab Width .25 in [6.35 mm], PCB Hole Diameter 5.16 mm [.203 in], Through Hole - Screw, Tin Plating, None, FASTON 250

[View on TE.com >](#)



Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

PCB Hole Diameter: **5.16 mm [.203 in]**

Profile Height from PCB: **7.48 mm [.295 in]**

Features

Product Type Features

Insertion Force	Normal
PCB Terminal Mounting Style	Stud Mount

Configuration Features

Stud Hole	Yes
Terminal Angle	45 °

Body Features

Finish	Matte
Plating Thickness	1.01 μm[40 μin]

Contact Features

Contact Plating Material	Tin
PCB Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Plating Material	Tin



Contact Underplating Material	None
Terminal Size	6.35
Terminal Orientation	45 Bend

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Screw
Product Terminates To	Printed Circuit Board

Dimensions

Stud Diameter	5.16 mm [.203 in]
PCB Hole Diameter	5.16 mm [.203 in]
Profile Height from PCB	7.48 mm [.295 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]

Industry Standards

CSA Certified	Yes
UL Rating	Recognized

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance













[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer






This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 181948-2 250 FASTON,TAB,TPBR</p>	 <p>TE Part # 41480 250 FASTON TAB TPBR</p>	 <p>TE Part # 42117-2 250 FASTON TAB TPBR</p>	 <p>TE Part # 63038-1 250 FASTON TAB TPBR</p>
 <p>TE Part # 61499-1 250 FASTON TAB TPBR</p>	 <p>TE Part # 63971-1 250 FASTON TAB TPBR</p>	 <p>TE Part # 60080-2 250 FASTON TAB TPBR</p>	 <p>TE Part # 181949-2 250 FASTON,TAB,TPBR</p>
 <p>TE Part # 1217002-1 250 FASTON,TAB, NPCST</p>	 <p>TE Part # 42095-1 250 FASTON TAB TPBR</p>	 <p>TE Part # 160650-2 250 FASTON,PCB TAB,TNBR</p>	 <p>TE Part # 62627-1 250 FASTON TAB TPST</p>



Also in the Series | FASTON 250



Documents

Product Drawings

250 FASTON TAB TPBR

English

CAD Files

Customer View Model

[ENG_CVM_CVM_61365-1_G.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_61365-1_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_61365-1_G.3d_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON Tabs](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_61365-1_092520181022_dmtec](#)

English

[MD_61365-1_092520181022_dmtec](#)

English

Agency Approvals

[CSA Certificate](#)

English

[CSA Certificate](#)

English