

626057-1 ✓ ACTIVE

FASTIN-FASTON | FASTIN-FASTON 110

TE Internal #: 626057-1

Crimp Terminal Housings, Tab, Tab Housing, 4 Position, Straight, Black, Polyamide, Mating Alignment, Cable Mount (Free-Hanging), FASTIN-FASTON 110

[View on TE.com >](#)



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Tab**

Housing Type: **Tab Housing**

Number of Positions: **4**

Terminal Orientation: **Straight**

Primary Product Color: **Black**

Features

Product Type Features

| | |
|---------------|------------------|
| Terminates To | Wire & Cable |
| Product Type | Terminal Housing |
| Sealable | No |
| Housing Type | Tab Housing |
| Insulated | No |

Configuration Features

| | |
|---------------------|---|
| Number of Positions | 4 |
|---------------------|---|

Body Features

| | |
|-----------------------|-------|
| Primary Product Color | Black |
|-----------------------|-------|

Contact Features

| | |
|--------------------------|----------|
| Terminal Type | Tab |
| Terminal Orientation | Straight |
| Contact Mating Retention | Without |



Mechanical Attachment

| | |
|---------------------------------------|----------------------------|
| Mating Alignment | With |
| Crimp Terminal Housing Mounting Style | Cable Mount (Free-Hanging) |

Housing Features

| | |
|--------------------|---------------|
| Housing Material | Polyamide |
| Centerline (Pitch) | 5 mm[.196 in] |

Dimensions

| | |
|--------|-------------------|
| Length | 27.33 mm[1.08 in] |
|--------|-------------------|

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 105 °C[-40 – 221 °F] |
|-----------------------------|----------------------------|

Packaging Features

| | |
|--------------------|------|
| Packaging Quantity | 6000 |
|--------------------|------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 180901
FF 250 TAB HSG 4P NYLON NAT



TE Part # 180908-5
FF 250 TAB HSG 2P NYLON BLACK



TE Part # 180916-5
FF 250 TAB HSG 1P NYLON BLACK



TE Part # 925015-1
FF 110 REC HSG 3P NYLON BLACK



TE Part # 626056-4
FASTIN-ON .110 HOUSING REC PRETO/BLACK



TE Part # 626057
FASTIN-ON 110 HOUSING TAB NAT 6.6 NYLON



TE Part # 280072
FF 375 TAB HSG 4P NYLON NAT



TE Part # 171445-1
FF 250 TAB HSG 14P ASSY CONN




TE Part # 1-171433-9
FF TAB HSG 6P NYLON BLACK




TE Part # 1-880298-0
FASTON .250 SERIES (6.3 MM) HOUSING


Also in the Series | FASTIN-FASTON 110




Automotive Housings(1)




Automotive Terminals(5)



Crimp Terminal Housings(34)



Insertion & Extraction Tools(3)



Documents

Product Drawings

[FASTIN-ON .110 HOUSING TAB NYLON 6/6](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_626057-1_H_c-626057-1-h.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_626057-1_H_c-626057-1-h.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_626057-1_H_c-626057-1-h.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[White Paper: Nylon Discoloration](#)

English

Product Specifications

[Application Specification](#)

English