

5-969484-2 ✓ ACTIVE

RAST | RAST 5 IDC Connectors

TE Internal #: 5-969484-2

Housing, Receptacle, Wire-to-Board, 2 Position, 5 mm [.196 in]  
Centerline, Crimp, 1 Row, Natural, Mating Retention, RAST 5 IDC  
Connectors

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **5 mm [.196 in]**

## Features

### Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Keying & Polarized Rib Location	1a,2a
Number of Positions	2
Number of Rows	1

### Contact Features

Contact Layout	Inline
Contact Type	Receptacle

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



### Mechanical Attachment

Locking Latch Between Cavity Number	1&2
Strain Relief	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

### Housing Features

Housing Material	PA 6.6
Centerline (Pitch)	5 mm [.196 in]
Housing Color	Natural

### Dimensions

Connector Length	10 mm [.39 in]
------------------	----------------

### Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Industry Standards

RAST Version	None
Glow Wire Rating	Glow Wire
UL Flammability Rating	UL 94V-2

### Packaging Features

Packaging Quantity	3200
Packaging Method	Carton

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224)



Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1241961-1  
STD TIM HOUSING MKII 2POS



TE Part # 969484-1  
STD TIM MK2 GEH 2P



TE Part # 5-969484-7  
STD TIM MK2 GEH 3P



TE Part # 1241961-3  
STD TIM HOUSING MKII 2POS



TE Part # 2-969484-2  
STD TIM MK2 GEH 2P



TE Part # 1-928344-2  
STD-TIMER GEH 2P



TE Part # 1-969484-7  
STD TIM MK2 GEH 3P



TE Part # 1955422-1  
STD TIM MK2 GEH 2P



TE Part # 2178930-3  
3P STD TIMER GEH V0 GWT



TE Part # 2322912-2  
STD TIMER PLUG HSG 2P GEH












TE Part # 4-969484-3  
STD TIM MK2 HSG 2P



TE Part # 6-969484-2  
STD TIM MK2 GEH 2P



## Also in the Series | RAST 5 IDC Connectors



## Documents

### Product Drawings

STD TIM MK2 GEH 2P

English

STD TIM MK2 GEH 2P

English

### CAD Files

3D PDF



3D

Customer View Model

[ENG\\_CVM\\_CVM\\_5-969484-2\\_H\\_c-5-969484-2-h.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-969484-2\\_H\\_c-5-969484-2-h.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_5-969484-2\\_H\\_c-5-969484-2-h.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

## Product Specifications

[Product Specification](#)

German

---

## Product Environmental Compliance

[TE Material Declaration](#)

English