

61248-1 ✓ ACTIVE


TE Internal #: 61248-1

Quick Disconnects, Tab, 20 – 18 AWG Wire Size, .51 – .82 mm² Wire Size, Straight, Brass, Tin Plating, Strip/Reel, F-Crimp, Open, Uninsulated

[View on TE.com >](#)



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.51 – .82 mm²**

Terminal Orientation: **Straight**

Contact Base Material: **Brass**

Features

Product Type Features

Terminates To	Wire & Cable
Wire Stop	No
Wire/Cable Type	Regular Wire
Sealable	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Contact Features

Quick Disconnect Terminal Type	Tab
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Accepts Wire Insulation Diameter Range	1.65 – 2.03 mm [.065 – .08 in]
Overall Length	23.72 mm [.93 in]
Receptacle Terminal Stock Thickness	.51 mm [.02 in]
Wire Size	.51 – .82 mm ²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

Industry Standards

UL Rating	Listed
-----------	--------

Packaging Features

Packaging Quantity	20000
Packaging Method	Strip/Reel

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)










EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on

requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 40626 FUSE TERMINAL RECEPTACLE 16-14 AWG TPBR</p>	 <p>TE Part # 1438246-1 SPLICE, BUTT, HEATER WIRE 18-16 AWG BR</p>	 <p>TE Part # 1438246-2 SPLICE, BUTT, HEATER WIRE 18-16AWG PTPBR</p>	 <p>TE Part # 63271-1 COIL TERMINAL TERMINAL 24-20 AWG PTPBR</p>
 <p>TE Part # 63863-1 TWIST LOCK RECEPTACLE 18-14 AWG TPPHBZ</p>	 <p>TE Part # 962907-2 FLACHSTECK 4,8 SPEZ</p>	 <p>TE Part # 1217440-8 STRAIN RELIEF,SPECIAL PH BRZ</p>	 <p>TE Part # 1217881-1 250 FUSE RCPT 020PTPBR</p>
 <p>TE Part # 61684-3 SPECIAL TAB TAB TNSL WIRE GPBR</p>	 <p>TE Part # 61684-5 SPECIAL TAB TAB TNSL WIRE NTPBR</p>	 <p>TE Part # 63723-2 RCPT TWISTLOK 20-16 0255 TPPHBZ</p>	 <p>TE Part # 63863-2 RCPT TWIST LK 18-14 0255PPHBZ</p>

Documents

Product Drawings

TAB INSULATION PIERCING 20-18 AWG TPCUBR

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_61248-1_J_c-61248-1-j.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_61248-1_J_c-61248-1-j.3d_igs.zip](#)

English

Customer View Model

61248-1

Quick Disconnects, Tab, 20 – 18 AWG Wire Size, .51 – .82 mm² Wire Size, Straight, Brass, Tin Plating, Strip/Reel, F-Crimp, Open, Uninsulated



[ENG_CVM_CVM_61248-1_J_c-61248-1-j.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Product Environmental Compliance](#)

[TE Material Declaration](#)

English