

61687-2 ✓ ACTIVE

FASTON | FASTON 187

TE Internal #: 61687-2

Quick Disconnects, Tab, 18 – 14 AWG Wire Size, .82 – 2.08 mm<sup>2</sup>

Wire Size, Mating Tab Width .187 in [4.75 mm], Straight, Brass, Tin

Plating, FASTON 187

[View on TE.com >](#)



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.82 – 2.08 mm<sup>2</sup>**

Mating Tab Width: **4.75 mm [ .187 in ]**

Mating Tab Thickness: **.81 mm [ .032 in ]**

## Features

### Product Type Features

Terminates To	Wire & Cable
Wire/Cable Type	Regular Wire
Wire Stop	No
Sealable	No

### Configuration Features

Connection Capacity	Single
---------------------	--------

### Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open



### Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

### Dimensions

Accepts Wire Insulation Diameter Range	3.05 – 3.81 mm [.12 – .15 in]
Receptacle Terminal Stock Thickness	.81 mm [.032 in]
Overall Length	17.14 mm [.675 in]
Wire Size	.82 – 2.08 mm <sup>2</sup>

### Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

### Industry Standards

CSA Certified	No
UL Rating	Listed

### Packaging Features

Packaging Quantity	3500
Packaging Method	Strip/Reel

### Other

Comment	Premilled dual stock thickness.
---------	---------------------------------

### Product Compliance











[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp</p>	 <p>TE Part # 63919-1 187 FASTON TAB 18-14 AWG TPBR</p>	 <p>TE Part # 61367-3 250 FASTON TAB 18-14 AWG TPBR</p>	 <p>TE Part # 2-2266314-1 OCEAN_2.0_Applicator-S-110F1800</p>
 <p>TE Part # 2-2266314-2 OCEAN_2.0_Applicator-S-110F1800A</p>	 <p>TE Part # 2266314-1 OCEAN_2.0_Applicator-S-110F1800</p>	 <p>TE Part # 2266314-2 OCEAN_2.0_Applicator-S-110F1800A</p>	 <p>TE Part # 7-2266314-1 OCEAN_2.0_Applicator-S-110F1800</p>
 <p>TE Part # 7-2266314-2 OCEAN_2.0_Applicator-S-110F1800A</p>	 <p>TE Part # 7-2266314-7 OCEAN_2.0_SPARE_PART_KIT-110F1800</p>		


Also in the Series | **FASTON 187**



Crimp Terminal Housings(41)




Insertion &amp; Extraction Tools(1)



Joints &amp; Splices(1)



PCB Terminals(48)



Quick Disconnects(213)



Splices(1)

## Documents

### Product Drawings

[187 FASTON TAB 18-14 AWG TPBR](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_61687-2\\_U.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_61687-2\\_U.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_61687-2\\_U.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[FASTON Tabs](#)

English

### Product Specifications

[Product Specification](#)

English

### Product Environmental Compliance

[MD\\_61687-2\\_10142015832\\_dmtec](#)

61687-2

Quick Disconnects, Tab, 18 – 14 AWG Wire Size, .82 – 2.08 mm<sup>2</sup> Wire Size, Mating  
Tab Width .187 in [4.75 mm], Straight, Brass, Tin Plating, FASTON 187



English

[MD\\_61687-2\\_10142015832\\_dmtec](#)

English