

69099 ✓ ACTIVE

AMP

TE Internal #: 69099

Hand Crimping Tools, Premium Crimp Tooling, Removable /Interchangeable, Hydraulic (8,200 psi), Head Assembly

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Tool Grade: Premium Crimp Tooling

Die Sets Type: Removable/Interchangeable

Power Technology Type: Hydraulic (8,200 psi)

Tooling Type: Head Assembly

### Features

#### Other

Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Power Technology Type	Hydraulic (8,200 psi)
Tooling Type	Head Assembly

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

















EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these

limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 605180-1 4/0 BUTT SPLICE &amp; HST PRE-PAK</p>	 <p>TE Part # 605181-1 1/0 BUTT SPLICE &amp; HST PRE-PAK</p>	 <p>TE Part # 46751-2 HYP8 AMPPOWER 250MCM DIE SET</p>	 <p>TE Part # 46750-2 HYP8 AMPPOWER 4/0AWG DIE SET</p>
 <p>TE Part # 45445 HYP8/10 SOLIS 4/0AWG DIE SET</p>	 <p>TE Part # 46752-2 HYP8 AMPPOWER 300MCM DIE SET</p>	 <p>TE Part # 45442 HYP8/10 SOLIS 3/0AWG DIE SET</p>	 <p>TE Part # 45436 HYP8/10 SOLIS 1/0AWG DIE SET</p>
 <p>TE Part # 69217 HYP8/10 SOLIS 6AWG DIE SET</p>	 <p>TE Part # 69216 HYP8/10 SOLIS 8AWG DIE SET</p>	 <p>TE Part # 69218 HYP8/10 SOLIS 4AWG DIE SET</p>	 <p>TE Part # 45433 HYP8/10 SOLIS 2AWG DIE SET</p>
 <p>TE Part # 45439 HYP8/10 SOLIS 2/0AWG DIE SET</p>	 <p>TE Part # 46765-3 HYP8 AMPPOWER 2AWG DIE SET</p>	 <p>TE Part # 46766-2 HYP8 AMPPOWER 1/0AWG DIE SET</p>	 <p>TE Part # 46767-2 HYP8 AMPPOWER 2/0AWG DIE SET</p>



## Documents

### Product Drawings

[HYP8 12-350MCM 18T HEAD](#)

English

### Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

### Product Specifications

[Safety Precautions](#)

French

[Safety Precautions](#)

English

### Instruction Sheets

[Hydraulic Crimping Systems](#)

English

[Hydraulic Crimping Systems](#)

French