

63453-1 ✓ ACTIVE


TE Internal #: 63453-1

Magnet Wire Terminals, Receptacle, 24 – 18 AWG Magnet Wire, .2 – .82 mm Magnet Wire, Crimp, Crimp Area Length 6.86 mm [.27 in], Tin Plating

[View on TE.com >](#)



Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Receptacle**

Mating Pin Diameter: **3.18 mm [.125 in]**

Accepts Wire Insulation Diameter (Max): **2.54 mm [.1 in]**

Accepts Wire Insulation Diameter Range: **1.52 – 2.54 mm [.06 – .1 in]**

Magnet Wire Size: **24 – 18 AWG**

Features

Product Type Features

Wire Insulation Support Retention Type	Insulation Support
Compatible With Discrete Wire Type	Magnet Wire, Solid
Sealable	No

Contact Features

Magnet Wire Terminal Type	Receptacle
Mating Pin Diameter	3.18 mm [.125 in]
Terminal Plating Material	Tin
Terminal Orientation	Straight

Termination Features

Termination Method to Wire & Cable	Crimp
Crimp Area Length	6.86 mm [.27 in]

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Housing Features



Housing Retention Force	Standard
-------------------------	----------

Dimensions

Terminal Height	6.1 mm[.24 in]
Accepts Wire Insulation Diameter (Max)	2.54 mm[.1 in]
Accepts Wire Insulation Diameter Range	1.52 – 2.54 mm[.06 – .1 in]
Magnet Wire Size	.2 – .82 mm
Stock Thickness (Magnet Wire Side)	.51 mm[.02 in]
Overall Product Length	22.1 mm[.87 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Aluminum, Copper
------------------------------------	------------------

Packaging Features

Packaging Quantity	10000
Packaging Method	Reel

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 360052-1 125 DIA CLSTR BLK</p>	 <p>TE Part # 360051-1 CLUSTER BLOCK</p>	 <p>TE Part # 520995-1 .125 CLUSTER BLOCK HSG</p>	 <p>TE Part # 1217186-1 CLUSTER BLOCK HOUSING</p>
 <p>TE Part # 1217200-1 CLUSTER BLOCK HOUSING</p>	 <p>TE Part # 1-1742539-3 CLUSTER BLOCK RECEPT,TPCuFeP</p>	 <p>TE Part # 1217261-1 HSG .125 CLUSTER BLOCK NAT</p>	 <p>TE Part # 1217181-1 CLUSTER BLOCK HSG.</p>
 <p>TE Part # 1217187-1 CLUSTER BLOCK HOUSING</p>	 <p>TE Part # 2-2150542-2 OCEAN-2.0-APPLICATOR-E-090F140F</p>	 <p>TE Part # 2150542-2 OCEAN-2.0-APPLICATOR-E-090F140F</p>	 <p>TE Part # 2161850-3 APT-5A DIRECT CONNECT</p>
 <p>TE Part # 567248-3 HDM 5EAPR090F140F G</p>	 <p>TE Part # 7-2150542-2 OCEAN-2.0-APPLICATOR-E-090F140F</p>	 <p>TE Part # 7-2150542-7 OCEAN_2.0_SPARE_PART_KIT-090F140F</p>	 <p>TE Part # 2161950-3 APT-5E DIRECT CONNECT</p>

Documents

Product Drawings

Cluster Block Recept Amplivar 400-1600

English



CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_63453-1_R.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63453-1_R.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63453-1_R.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Magnet Wire Terminals & Splices](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_63453-1_100720142219_dmtec](#)

English

[MD_63453-1_100720142219_dmtec](#)

English