

63459-3 ✓ ACTIVE

MAG-MATE


TE Internal #: 63459-3

Magnet Wire Terminals, Tab, Mating Tab Width .25 in [6.35 mm],
Size 4, 16 – 15 AWG Magnet Wire, 1.29 – 1.45 mm Magnet Wire,
MAG-MATE

[View on TE.com >](#)



Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Tab**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.8 mm [.032 in]**

Compatible With Cavity Size: **Size 4**

Magnet Wire Size: **16 – 15 AWG**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Body Features

Body Shape	Wide
------------	------

Compatible With Cavity Size	Size 4
-----------------------------	--------

Contact Features

Magnet Wire Terminal Type	Tab
---------------------------	-----

Mating Tab Width	6.35 mm [.25 in]
------------------	------------------

Mating Tab Thickness	.8 mm [.032 in]
----------------------	-----------------

Terminal Plating Material	Tin
---------------------------	-----

Terminal Orientation	Straight
----------------------	----------

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment



Contact Mating Retention Type	Hole
-------------------------------	------

Dimensions

Terminal Height	12.83 mm[.505 in]
Magnet Wire Size	1.29 – 1.45 mm
Stock Thickness (Magnet Wire Side)	.51 mm[.02 in]
Overall Product Length	24.18 mm[.952 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Aluminum, Copper
------------------------------------	------------------

Identification Marking

Identification Number	40
-----------------------	----

Packaging Features

Packaging Quantity	5000
Packaging Method	Reel, Reel/Carton

Other

Comment	After insertion into plastic cavity, tab portion can not be bent over. The body is potted in only., Two magnet wires may be terminated in the same terminal slot if diameters are equal., Varnish resist coating.
---------	---

Product Compliance












[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 63598-1 MAG-MATE 250 F-TAB TPBR</p>	 <p>TE Part # 63881-1 MAG-MATE 250 F. TAB TPBR</p>	 <p>TE Part # 63816-1 TAB, MAG-MATE 250F TPBR</p>	 <p>TE Part # 63882-1 MAG-MATE 250 F-TAB TPBR</p>
 <p>TE Part # 63064-1 MAG-MATE 250 F TAB 032 TPBR</p>	 <p>TE Part # 63495-1 MAG-MATE 250 F-TAB TPBR</p>	 <p>TE Part # 3-1579018-3 INSERTION TOOL</p>	 <p>TE Part # 62923-1 MAG-MATE 250 F TAB 032 TPBR</p>
 <p>TE Part # 63371-1 MAG-MATE 250 F TAB TPBR</p>	 <p>TE Part # 63425-1 MAG MATE 250F TAB #12 TPBR.</p>	 <p>TE Part # 63816-2 TAB 250 FAST MM 14-13 TPBR</p>	

Also in the Series | **MAG-MATE**



Insertion & Extraction Tools(7)



Magnet Wire Terminals(462)



PCB Terminals(1)

Documents

Product Drawings

MAG-MATE 250 F-TAB 15-16 TPBR

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_63459-3_Z.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63459-3_Z.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63459-3_Z.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English