

735411 ✓ ACTIVE

ELECTRO-TAP

TE Internal #: 735411


Splices, 11 – 10 AWG Wire Size, 4 – 6 mm² Wire Size, 7894 – 11841

CMA Wire Size, Brass, Yellow, Tap Splice Splice, ELECTRO-TAP

[View on TE.com >](#)



Terminals & Splices > Splices



Wire Size: 7894 – 11841 CMA

Sealable: No

Accepts Wire Insulation Diameter Range: 5 mm [.197 in]

Features

Product Type Features

Discrete Wire Type	Solid or Stranded
Splice Accessory Type	Tap Cover
Sealable	No
Splice Type	Tap Splice
Serrated	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Body Features

Plating Material	Tin
Primary Product Material	Brass
Primary Product Color	Yellow

Contact Features

Contact Plating Material	Tin
--------------------------	-----

Termination Features



Termination Method	Crimp
--------------------	-------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Housing Features

Housing Material	Nylon
------------------	-------

Dimensions

Tap Wire Size	4 – 6 mm ²
---------------	-----------------------

Wire Size	7894 – 11841 CMA
-----------	------------------

Accepts Wire Insulation Diameter Range	5 mm [.197 in]
--	----------------

Overall Product Length	49.76 mm [1.959 in]
------------------------	---------------------

Usage Conditions

Insulation Option	Fully Insulated
-------------------	-----------------

Operating Temperature Range	105 °C [221 °F]
-----------------------------	-----------------

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	100
--------------------	-----

Packaging Method	Loose Piece
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

Also in the Series | **ELECTRO-TAP**

Documents

Product Drawings

ELECTRO TAP, 4 - 6 mm², 11 - 10 AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_735411_D.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_735411_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_735411_D.3d_stp.zip](#)

English

[3D PDF](#)

English

Customer View Model

[ENG_CVM_735411_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_735411_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_735411_A.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ELECTRO-TAP CABLE CONNECTOR/SPLICE](#)

English