

69693-1 ✓ ACTIVE

AMP

TE Internal #: 69693-1

Hand Crimping Tools, Premium Crimp Tooling, Not Releasable,  
Not Adjustable, Fixed In Tool, MIL Spec / TE Product Specification  
(114-)

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **MIL Spec, TE Product Specification (114-)**

TE Certification: **Yes – Certificate Included**

## Features

### Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Manual
Tooling Type	T Head Hand Tool

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content













Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 50840 TERMINAL,PIDG PTFE R 14 8</p>	 <p>TE Part # 50834 TERMINAL,PIDG PTFE R 18-16 4</p>	 <p>TE Part # 50836 TERMINAL,PIDG PTFE R 18-16 8</p>	 <p>TE Part # 50840-1 TERMINAL,PIDG PTFE R 14 10</p>
 <p>TE Part # 50836-1 TERMINAL,PIDG PTFE R 18-16 10</p>	 <p>TE Part # 50839-1 PIDG PTFE STRATO RING 14 6</p>	 <p>TE Part # 332453 TERMINAL,PIDG PTFE R AU 18-16 6</p>	 <p>TE Part # 1-332454-0 TERMINAL,PIDG PTFE R AU 18-16</p>
 <p>TE Part # 50835 TERMINAL,PIDG PTFE R 18-16 6</p>	 <p>TE Part # 50837 TERMINAL,PIDG PTFE R 18-16 1/4</p>	 <p>TE Part # 1-332438-0 TERMINAL,PIDG PTFE R AU 14 6</p>	 <p>TE Part # 50841 TERMINAL,PIDG PTFE R 14 1/4</p>

## Documents

## Product Drawings

T-HEAD PIDG STRATO 18-14 ASSY



English

---

**Datasheets & Catalog Pages**

**Bottoming Dies**

English

---

**Instruction Sheets**

**Instruction Sheet (U.S.)**

English