




Wire Protection & Management > Interconnect Devices > Shielded Contacts



Shielded Contact Product Type: **Contact**

Shielded Contact Wire & Cable Type: **Coaxial**

Shielded Contact Style: **Pin**

Shielded Contact Size: **16**

Features

Product Type Features

Shielded Contact Product Type	Contact
Shielded Contact Wire & Cable Type	Coaxial

Contact Features

Shielded Contact Style	Pin
Shielded Contact Size	16

Termination Features

Termination Method	Solder
--------------------	--------

Usage Conditions

Operating Temperature (Max)	150 °C
-----------------------------	--------

Industry Standards

Government Qualified	No
----------------------	----

Other

Comment	Commercial item.
---------	------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

Current ECHA Candidate List: JUNE 2022
(224)

Candidate List Declared Against: JUL 2021
(219)

SVHC > Threshold:

Pb (37% in Solder)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Documents

Product Drawings

[D-602-0278](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_845569-000_O.2d_dxf.zip](#)

English

[3D PDF](#)

3D



Customer View Model

[ENG_CVM_CVM_845569-000_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_845569-000_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654025_Sec8_D-602](#)

English

[Raychem Electrical Interconnect Products](#)

English

Product Specifications

[Termination Procedure for Subminiature SolderTact Contacts for Coaxial Cable D-602-0219, D-602-0278 and D-602-0279](#)

English