



CII

TE Internal #: 6-1618386-9

Power Relays, Solid State, 3.8 VDC Coil Voltage, 1 Form A (NO), 250 VAC Contact Switching Voltage (Max), 250 VAC Contact Voltage, Tray/Box, Screw

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Solid State**

Coil Voltage Rating: **3.8 VDC**

Contact Arrangement: **1 Form A (NO)**

Contact Current Rating (Max): **10 A**

Contact Switching Voltage (Max): **250 VAC**

**Features**

**Product Type Features**

Enclosure Type	Hermetically Sealed
Output Type	DC
Screening Level	Y
Power Relay Type	Solid State

**Electrical Characteristics**

Output Current Rating	10 A
Output Voltage Rating (AC Relays)	250 Vrms
Vibration	30G's, 10 – 3000Hz
Actuating System	AC
Shock	100G's, 6ms
Coil Voltage Rating	3.8 VDC
Contact Switching Voltage (Max)	250 VAC
Contact Voltage Rating	250 VAC

**Contact Features**

Contact Arrangement	1 Form A (NO)
Contact Current Rating (Max)	10 A
Relay Terminal Type	Screw Terminals



### Termination Features

Relay Termination Type	Screw Terminals
------------------------	-----------------

### Mechanical Attachment

Relay Mounting Type	Screw
---------------------	-------

### Dimensions

Dimensions (L x W x H) (Approximate)	50.8 x 25.4 x 22.9 mm
--------------------------------------	-----------------------

### Usage Conditions

Operating Temperature Range	-55 – 95 °C
-----------------------------	-------------

### Packaging Features

Packaging Method	Tray/Box
------------------	----------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 5-1617353-5  
DS11-1Y=



TE Part # 8-1618387-7  
PS12-1W=SOLID STATE RELAY, 10A /250VAC



TE Part # 2-1617070-7  
1621-C-2001 = 1600 FIXED OPERA



TE Part # 3-1618400-8  
DS11-1005T=SOLID STATE RELAY

TE Part # 1617827-4  
4610-C-1600 Fixed Timer

TE Part # 1617827-5  
1621-C-0700 = 1600 FIXED OPERA

TE Part # 9-1617814-0  
PS10-1Y = 25A HP SSR

TE Part # 1617815-3  
PS10-2Y = 25A HP SSR

TE Part # 1-1617827-9  
1440-1a=PHASE SENSOR

TE Part # 2-1617827-1  
1440-1c=PHASE SENSOR

## Documents

### Product Drawings

[PS12-1Y = SOLID STATE RELAY, 10A/250VAC](#)

English

### Datasheets & Catalog Pages

[5-1773450-5\\_sec10\\_PS12](#)

English