




Connectors &gt; Power Connectors &gt; Rectangular Power &gt; Rectangular Power Connectors

Rectangular Power Connector Type: **Housing**Connector & Housing Type: **Plug**Connector System: **Wire-to-Wire**Number of Positions: **1**Centerline (Pitch): **3.68 mm [.145 in]**

## Features

### Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Configuration Features

Number of Positions	1
Number of Signal Positions	1
Number of Rows	1

### Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

### Contact Features

Contact Layout	Inline
Multiple Contact Types	Without



Contact Retention Within Housing	Without
----------------------------------	---------

Contact Type	Pin
--------------	-----

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Wire/Cable Type	Discrete Wire
-----------------	---------------

### Mechanical Attachment

Panel Mount Feature	Without
---------------------	---------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

### Housing Features

Centerline (Pitch)	3.68 mm [.145 in]
--------------------	-------------------

Housing Color	Natural
---------------	---------

Housing Material	Nylon
------------------	-------

### Dimensions

Wire Size	394.71 – 1776.17 CMA
-----------	----------------------

Accepts Wire Insulation Diameter Range	1.27 – 2.79 mm [.05 – .11 in]
--	-------------------------------

Length	19.3 mm [.76 in]
--------	------------------

### Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Insertion Force	17.8 Newton
-----------------	-------------

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

Agency/Standard Number	E28476
------------------------	--------

Agency/Standard	CSA, UL
-----------------	---------

UL Rating	Recognized
-----------	------------

CSA File Number	LR7189
-----------------	--------

VDE Tested	No
------------	----

### Packaging Features

Packaging Method	Package
------------------	---------

Packaging Quantity

1

## Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

BFR/CFR/PVC Free, but Br/Cl &gt;900 ppm in other sources.

Solder Process Capability

Not applicable for solder process capability

















### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>





## Compatible Parts





 <p>TE Part # 640391-1 .062 COMM P&amp;S PIN 24-30 PTPBR</p>	 <p>TE Part # 350629-1 .062 COMM P&amp;S PIN 18-24 PTPBR</p>	 <p>TE Part # 350628-2 .062 COMM P&amp;S SOK PTPPHBZ</p>	 <p>TE Part # 640392-1 .062 COMM P&amp;S SOK 24-30 PTPBR</p>
 <p>TE Part # 350629-8 .062 COMM P&amp;S PIN PRE TIN/PHBZ</p>	 <p>TE Part # 794019-1 .062 CP&amp;S SOK PTPBR L/P 30-24</p>	 <p>TE Part # 350628-1 .062 COMM P&amp;S SOK 18-24 PTPBR</p>	 <p>TE Part # 770983-1 .062 COMM P&amp;S PIN 18-24 PTPBR</p>
 <p>TE Part # 350628-6 .062 COMM P&amp;S SOK AUNI/PHBZ</p>	 <p>TE Part # 794046-1 .062 COMM P&amp;S SOK 24-30 PTPBR</p>	 <p>TE Part # 640392-2 .062 COMM P&amp;S SOK 24-30PTPHBZ</p>	 <p>TE Part # 794016-1 .062 CP&amp;S SOK PTPBR L/P 24-18</p>
 <p>TE Part # 794018-1 .062 CP&amp;S PIN PTPBR L/P 30-24</p>	 <p>TE Part # 794103-1 .062 COMM P&amp;S LANCELESS SCKT</p>	 <p>TE Part # 350628-8 .062 CP&amp;S SOK 18-24 PTPBR PLST</p>	 <p>TE Part # 640392-5 .062 COMM P&amp;S SOCKET AUPLBR</p>

Also in the Series | Commercial Pin and Socket Connectors


 <p>Connector Contacts(3)</p>	 <p>Crimp Wire Pins, Tabs &amp; Ferrules(1)</p>	 <p>Insertion &amp; Extraction Tools(3)</p>	 <p>Power Contacts(40)</p>
--	--	--	---



Rectangular Connector Housings(11)



Rectangular Power Connectors(88)



Standard Rectangular Connectors(4)

## Documents

### Product Drawings

[01P .062 COMM P&S PLUG](#)

English

### CAD Files

[3D PDF](#)

English

Customer View Model

[ENG\\_CVM\\_770278-1\\_C.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_770278-1\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_770278-1\\_C.3d\\_stp.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_770278-1\\_G.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_770278-1\\_G.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_770278-1\\_G.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[SOFT\\_SHELL\\_PIN\\_AND\\_SOCKET\\_CONNECTORS\\_CATALOG](#)

English

### Product Specifications

[Application Specification](#)



English

---

[Agency Approvals](#)

[Agency Approval Document](#)

English