

794192-1 ✓ ACTIVE

MATE-N-LOK | Mini-Universal MATE-N-LOK 2

TE Internal #: 794192-1

Rectangular Power Connectors, Housing, Plug, Wire-to-Board /


Wire-to-Wire, 8 Position, 4.14 mm [.162 in] Centerline, Mini-

Universal MATE-N-LOK 2

[View on TE.com >](#)



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board, Wire-to-Wire**

Number of Positions: **8**

Centerline (Pitch): **4.14 mm [.162 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	8
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Multiple Contact Types	Without
Contact Retention Within Housing	Without
Contact Type	Socket

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	4.14 mm [.162 in]
Housing Color	Natural
Housing Material	Nylon

Dimensions

Row-to-Row Spacing	4.14 mm [.162 in]
--------------------	-------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Assembly Integration Feature	Without
Circuit Application	Power & Signal

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire
UL Rating	Recognized
Agency/Standard Number	E28476
VDE Tested	No
Agency/Standard	UL

Packaging Features

Packaging Method	Bag
Packaging Quantity	400

Other

For Use With	Mini-Universal MATE-N-LOK 2 Cap Housing /PC Board Pin Headers Header
--------------	--

Product Compliance




For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 1-794228-0 MINI UMNL2 PIN 22-18 AWG AU LP</p>	 <p>TE Part # 794065-1 08P MINI UMNL HDR W/DH SN</p>	 <p>TE Part # 770970-1 08P MINI UMNL R/A HDR ASSY SN</p>	 <p>TE Part # 794224-1 MINI UMNL2 PIN 30-26 AWG SN LP</p>
 <p>TE Part # 1-794073-0 08P MINI UMNL HDR W/O DH SN LF</p>	 <p>TE Part # 1-794065-0 08P MINI UMNL HDR W/DH SN</p>	 <p>TE Part # 1-794065-1 08P MINI UMNL HDR W/DH AU LF</p>	 <p>TE Part # 794193-1 08P MINI UMNL2 CAP HSG UL94V0</p>



Also in the Series | Mini-Universal MATE-N-LOK 2



Documents

Product Drawings

08P MINI UMNL2 PLUG HSG UL94V0

English

CAD Files

3D PDF

3D

Customer View Model



[ENG_CVM_CVM_794192-1_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_794192-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_794192-1_F.3d_stp.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_794192-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_794192-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_794192-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English