

794901-1 ✓ ACTIVE

MATE-N-LOK | Universal MATE-N-LOK

TE Internal #: 794901-1

Rectangular Power Connectors, Housing, Plug, Wire-to-Board /
Wire-to-Wire, 3 Position, 6.35 mm [.25 in] Centerline, Wire & Cable,
Universal MATE-N-LOK

[View on TE.com >](#)



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board, Wire-to-Wire**

Number of Positions: **3**

Centerline (Pitch): **6.35 mm [.25 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Layout	Inline
Multiple Contact Types	Without
Contact Retention Within Housing	Without



Contact Type	Socket
--------------	--------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Mount Feature	Without
---------------------	---------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	6.35 mm [.25 in]
--------------------	------------------

Housing Color	Black
---------------	-------

Housing Material	Nylon
------------------	-------

Dimensions

Width	14.73 mm [.579 in]
-------	--------------------

Height	27.43 mm [1.08 in]
--------	--------------------

Length	20.32 mm [.8 in]
--------	------------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Assembly Integration Feature	Without
------------------------------	---------

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

Industry Standards

CSA Rating	Certified
------------	-----------

UL Flammability Rating	UL 94V-2
------------------------	----------

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

Agency/Standard Number	E28476
------------------------	--------

Agency/Standard	CSA, UL
-----------------	---------

UL Rating	Recognized
-----------	------------

CSA File Number	LR7189
-----------------	--------

VDE Tested	Yes
------------	-----

Packaging Features



Packaging Method	Package
Packaging Quantity	1

Other

For Use With	Appropriate Universal MATE-N-LOK Cap or Header
--------------	--

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 1-480701-4 03P UMNL CAP HSG YELL</p>	 <p>TE Part # 1-350767-9 03P UMNL V0 CAP HSG BLACK</p>	 <p>TE Part # 1-480701-2 03P UMNL CAP HSG RED</p>	 <p>TE Part # 770025-1 03P UMNL II IN-LINE CAP HSG KIT</p>
 <p>TE Part # 350767-1 03P UMNL CAP HSG V0</p>	 <p>TE Part # 794899-1 04P UMNL HI TEMP PLUG HSG</p>	 <p>TE Part # 1-480701-0 03P UMNL CAP HSG NATL</p>	 <p>TE Part # 8-794535-1 06P UMNL PLUG HSG 150C BLK, SP</p>
 <p>TE Part # 1586849-1 03P UMNL CAP HSG NATL, GW</p>	 <p>TE Part # 794900-1 03P UMNL HI TEMP CAP HSG</p>	 <p>TE Part # 794096-1 06P UMNL PLUG</p>	 <p>TE Part # 1-480700-9 03P UMNL PLUG HSG BLK</p>
 <p>TE Part # 1-480701-9 03P UMNL CAP HSG BLK</p>	 <p>TE Part # 1-350777-9 02P UMNL V0 PLUG HSG BLACK</p>	 <p>TE Part # 1-480701-6 03P UMNL CAP HSG BLU</p>	 <p>TE Part # 1586702-1 02P UMNL PLUG HSG NATL LEAD IN</p>
 <p>TE Part # 2-480701-0 03P UMNL CAP HSG NATL</p>	 <p>TE Part # 1-480701-8 03P UMNL CAP HSG GRY</p>	 <p>TE Part # 1-350766-9 03P UMNL V0 PLUG HSG BLACK</p>	 <p>TE Part # 770048-1 03P UMNL II CAP REAR 94VO</p>

Also in the Series | [Universal MATE-N-LOK](#)




Circular Power Connectors(2)



Connector Contacts(11)



Insertion & Extraction Tools(4)



Power Contacts(207)



Rectangular Boots & Strain Relief(35)



Rectangular Connector Adapters(7)



Rectangular Connector Hardware(1)




Rectangular Connector Housings(2)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(4)



Rectangular Connector Seals(26)



Rectangular Power Connectors(728)

Documents

Product Drawings

03P UMNL HI TEMP PLUG HSG

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_794901-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_794901-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_794901-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Agency Approvals

[VDE Certificate](#)

English