

**AMPLIMITE**

TE Internal #: 7-1393740-8

PCB D-Sub Connectors, Plug, Cable-to-Board, 9 Position, 2.74 mm [.108 in] Centerline, 2 Row, Size 1, Round, Standard Profile, Vertical

[View on TE.com >](#)

Connectors &gt; D-Shaped Connectors &gt; D-Sub Connectors &gt; PCB D-Sub Connectors &gt; D-Sub Plug Assembly: Standard, Vertical, Shell Size 1, 2.74mm

Connector & Housing Type: **Plug**Connector System: **Cable-to-Board**Number of Positions: **9**Centerline (Pitch): **2.74 mm [.108 in]**Number of Rows: **2**[All D-Sub Plug Assembly: Standard, Vertical, Shell Size 1, 2.74mm \(50\)](#)**Features****Product Type Features**

Grounding Indents	With
Grounding Straps	With
Grounded	Yes
Boss on Shield	With
Shell Type	Front Metal Shell
Connector & Housing Type	Plug
Connector System	Cable-to-Board
D-Sub Shell Size	1
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Product Type	Connector

**Configuration Features**

Number of Positions	9
Number of Rows	2
PCB Mount Orientation	Vertical
Preloaded	Yes

**Body Features**



Plastic	No
Connector Profile	Standard
Post Size	.7 mm
Color	Gray
Shell Material	Steel
Shell Plating Material	Tin

#### Contact Features

Contact Mating Area Plating Material	Gold
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Shape & Form	Round
	30 µin

#### Termination Features

Grounding Clips	Without
Termination Method to Printed Circuit Board	Through Hole - Solder
Termination Post Length	3.2 mm[.126 in]

#### Mechanical Attachment

PCB Mount Alignment	With
Panel Mount Feature	Without
PCB Mount Retention	With
PCB Mount Retention Type	Solder Tail
Mating Retention	With
Mating Retention Type	Threaded Insert
Connector Mounting Type	Board Mount
Mounting Hole Diameter	3.1 mm

#### Housing Features

Centerline (Pitch)	2.74 mm[.108 in]
Housing Material	PBTP GF

#### Dimensions

Row-to-Row Spacing	2.84 mm[.112 in]
PCB Thickness (Recommended)	1.5 mm[.059 in]



### Operation/Application

Circuit Application	Signal
---------------------	--------

### Industry Standards

Approved Standards	DIN 41652
UL Flammability Rating	UL 94V-0

### Packaging Features

Packaging Method	Tray
Packaging Quantity	70

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (.35% in Component part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



## Documents

### Product Drawings

[V42254A2216C209=SUB D STIFTLEI](#)

English

### CAD Files

[3D PDF](#)

3D

[3D PDF](#)

English

Customer View Model

[ENG\\_CVM\\_7-1393740-8\\_C.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_7-1393740-8\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_7-1393740-8\\_C.2d\\_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English