



TKM

TE Internal #: 7-1768048-7

Standard Labels, Label Width 25 mm [1 in], Label Height 2 in [50 mm], Vinyl, Label Thickness 80 Micron, TKM

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > TKM Self Laminating Vinyl Labels

Label Type: **Self-Laminating**Label Style: **Die-Cut**Label Adhesive Type: **Permanent Pressure Sensitive Acrylic Adhesive**UL Listed: **No**Label Width: **25 mm [1 in]**[All TKM Self Laminating Vinyl Labels \(4\)](#)**Features****Product Type Features**

Printable Label Height	15 mm[.06 in]
Label Type	Self-Laminating

Dimensions

Compatible Cable Diameter (Min)	4.8 mm[.188 in]
Compatible Cable Diameter (Max)	11.1 mm[.439 in]

Usage Conditions

Operating Temperature Range	-30 – 120 °C[-22 – 248 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	3
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	25 mm[1 in]
Label Height	50 mm[2 in]
Label Material	Vinyl
Label Thickness	80 Micron

Industry Standards



UL Listed	No
-----------	----

Packaging Features

Packaging Quantity	90
Packaging Method	Booklet

Other

Label Adhesive Type	Permanent Pressure Sensitive Acrylic Adhesive
---------------------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | TKM



Documents

Product Drawings

[TKM50WE-N](#)

English

Datasheets & Catalog Pages

[IDENTIFICATION SELECTION GUIDE](#)

English

[TKM BKM self laminating labels](#)

English