

880125 ✓ ACTIVE

MATE-N-LOK | Commercial MATE-N-LOK


TE Internal #: 880125

Rectangular Connector Housings, Wire-to-Wire, 9 Position, .24 in [6.1 mm] Centerline, 3 Row, Nylon GF, Receptacle, Pin, Commercial MATE-N-LOK

[View on TE.com >](#)



Connectors > Rectangular Connectors > Rectangular Connector Housings



Connector System: **Wire-to-Wire**

Number of Positions: **9**

Centerline (Pitch): **6.1 mm [.24 in]**

Row-to-Row Spacing: **3.1 mm [.24 in]**

Number of Rows: **3**

Features

Product Type Features

Connector System	Wire-to-Wire
Connector & Housing Type	Receptacle
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector Type	Housing
Product Type	Connector

Configuration Features

Number of Positions	9
Number of Rows	3

Electrical Characteristics

Voltage	250 VAC
Operating Voltage	250 VAC

Body Features

Color	Natural
-------	---------



Contact Features

Contact Layout	Matrix
Contact Type	Pin

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	6.1 mm [.24 in]
Housing Material	Nylon GF
Housing Color	Natural

Dimensions

Row-to-Row Spacing	3.1 mm [.24 in]
Height	26.8 mm
Length	28.7 mm
Width	20.93 mm

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Identification Marking

Circuit Identification Feature	With
--------------------------------	------

Industry Standards

Agency/Standard	UL
UL File Number	E28476
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	1400
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------











EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 350389-1 .140 DIA PIN 20-14 PTPBR L/P</p>	 <p>TE Part # 1-480585-0 09P .140 MNL PLUG NAT</p>	 <p>TE Part # 925660-2 140 DIA PIN</p>	 <p>TE Part # 925660-1 .140 DIA PIN</p>
 <p>TE Part # 925715-1 M-N-L PIN TPBR</p>	 <p>TE Part # 350201-2 .140 DIA PIN 14-10 PTPPHBZ</p>	 <p>TE Part # 61627-1 .140 DIA PIN 20-14 PTPBR</p>	 <p>TE Part # 927841-2 MNL STIFT 3,5 MM</p>



TE Part # 350201-1
.140 DIA PIN 14-10 PTPBR



TE Part # 880685-2
.140 DIA PIN



TE Part # 926988-1
MNL STIFT 3,5 MM



TE Part # 925715-2
MATENLOK PIN .140



TE Part # 925713-2
.140 DIA PIN



TE Part # 925713-1
M-N-L PIN TPBR



TE Part # 350391-1
.140 DIA PIN 14-10 PTPBR L/P



TE Part # 365046-1
09P.M-N-L.PIN HDR.



TE Part # 61627-2
.140 DIA PIN 20-14 PTPPHBZ



TE Part # 880124
9 CIR PLUG 140DIA PANEL MT NAT




TE Part # 925662-1
9140 DIA PIN



TE Part # 927858-2
KONTAKTSTIFT 3,5 MM


Also in the Series | Commercial MATE-N-LOK




Connector Contacts(26)




Crimp Wire Pins, Tabs & Ferrules(3)




Insertion & Extraction Tools(5)



Power Contacts(129)




Rectangular Caps & Covers(2)



Rectangular Connector Housings(17)




Rectangular Connector Seals(1)



Rectangular Power Connectors(170)



Standard Circular Connectors(4)



Standard Rectangular Connectors(10)



Wire-to-Board Connector Contacts(1)

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_880125_J.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_880125_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_880125_J.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_880125_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_880125_G.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_880125_G.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Agency Approvals

Agency Approval Document

English