



Kilovac | Kilovac CAP200

TE Internal #: 9-1618380-3

DC Contactors, 1 Form A, SPST-NO with Aux. Contacts, 22 AWG Wire Size, .34 mm² Wire Size, 500 A, 36 VDC Coil Voltage, Kilovac CAP200

[View on TE.com >](#)

Relays, Contactors & Switches > Contactors > Mil-Aero Contactors > DC Contactors



DC Contactor Contact Arrangement: **1 Form A, SPST-NO with Aux. Contacts**

Wire Size: **.34 mm²**

DC Contactor Contact Current Rating: **500 A**

Coil Voltage (Max): **36 VDC**

Features

Product Type Features

Product Classification	Relays - Contactors
Product Type	Contactor
Product Category	Electromechanical Relays
Contactor Type	Sealed
Terminal Configuration	M8 x 1.25 Stud

Configuration Features

Auxiliary Switch Contact Arrangement	1 Form A, SPST-NO
--------------------------------------	-------------------

Electrical Characteristics

Actuating System	DC
Coil Voltage (Max)	36 VDC
DC Contactor Coil Resistance	3.14 Ω
DC Contactor Coil Voltage Rating	9 – 36 VDC
DC Contactor Contact Switching Voltage (Max)	900 VDC

Contact Features

DC Contactor Contact Arrangement	1 Form A, SPST-NO with Aux. Contacts
DC Contactor Contact Current Rating	500 A
Pole Configuration	1

Termination Features

Coil Termination	Wire
------------------	------



Mechanical Attachment

DC Contactor Mounting Type	Bottom
----------------------------	--------

Dimensions

Coil Wire Length	390 mm[15.3 in]
Wire Size	.34 mm ²

Packaging Features

Packaging Method	Individual
------------------	------------

Other

Torque	80 – 100 in-lbs
--------	-----------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.



Compatible Parts



Also in the Series | Kilovac CAP200



Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_9-1618380-3_H.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1618380-3_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1618380-3_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1773450-5_sec7_CAP200](#)

English