

91555-1 ✓ ACTIVE

AMP

TE Internal #: 91555-1

Hand Crimping Tools, Premium Crimp Tooling, Not Releasable,  
Not Adjustable, Fixed In Tool, TE Product Specification (114-)

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Yes – Certificate Included**

## Features

### Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Electric, Manual
Tooling Type	CERTI-CRIMP II, Straight Action Hand Tool

## Product Compliance







[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 66010-2 AMP BLADE RECP LP</p>	 <p>TE Part # 66005-2 AMP BLADE RECP PLTD 30 AU</p>	 <p>TE Part # 66010-3 AMP BLADE RECP LP MIL</p>	 <p>TE Part # 5-531586-3 AMP BLADE II RECP PLTD 30 DPLX</p>
 <p>TE Part # 531586-3 AMP BLADE II RECP PLTD 30 DPLX</p>	 <p>TE Part # 66005-3 AMP BLADE RECP MIL PLTD 50 AU</p>	<p>TE Part # 531586-1 AMPBLADE II RCPT UNPLTD</p>	<p>TE Part # 66005 TERMINAL GROUP NUMBER</p>
<p>TE Part # 66005-1 AMP BLADE RECP STMPD</p>	<p>TE Part # 66010 TERMINAL GROUP NUMBER</p>	<p>TE Part # 66010-1 CONT-AMP BLADE L P</p>	

## Documents

[Datasheets & Catalog Pages](#)

[Bottoming Dies](#)

English

[Instruction Sheets](#)



[Instruction Sheet \(U.S.\)](#)

English