



Wire Protection & Management > Heat Shrink Shapes > Sealing Sleeves



Sealing Sleeve Product Type: **Heat Shrink Repair Sleeve**

Adhesive Inside Diameter: **1.68 mm [.066 in]**

Sleeve Inside Diameter: **2.74 mm [.108 in]**

Primary Product Color: **Red**

Wire Size: **22 – 20 AWG**

Features

Product Type Features

Sealing Sleeve Product Type	Heat Shrink Repair Sleeve
-----------------------------	---------------------------

Body Features

Primary Product Color	Red
-----------------------	-----

Dimensions

Conductor Outside Diameter	1.1 – 1.5 mm [.043 – .059 in]
Adhesive Cut Length	21.59 mm [.85 in]
Adhesive Inside Diameter	1.68 mm [.066 in]
Sleeve Inside Diameter	2.74 mm [.108 in]
Wire Size	22 – 20 AWG
Sleeve Cut Length	19.05 mm [.75 in]

Usage Conditions

Operating Temperature Range	-65 – 150 °C
-----------------------------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUL 2021 (219)

Does not contain REACH SVHC

Halogen Content

Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Documents

Product Drawings

[D-150-C-12](#)

English

Datasheets & Catalog Pages

[1654025_Sec8_D-150_D-500_DK-621](#)

English

Harness Repair Products Quick Reference Guide

English

Product Specifications

[Side Entry Insulation Damage Repair Sleeve \(SEIDRS\)](#)

English



Installation Procedure for Series D-150-C-1X. Side Entry Insulation Damage Repair Sleeve (SEIDRS)

English