



CM-SCE-TP

TE Internal #: F82125-000

Printable Tags, Military, -55 – 135 °C [-67 – 221 °F], Yellow, CM-SCE-TP

[View on TE.com >](#)

Identification & Labeling > Printable Tags > CM-SCE-TP Military Grade Markers



Printable Tag Grade: **Military**

Operating Temperature Range: -55 – 135 °C [-67 – 221 °F]

Primary Product Color: **Yellow**

[All CM-SCE-TP Military Grade Markers \(8\)](#)

**Features**

**Product Type Features**

Printable Tag Grade	Military
---------------------	----------

**Body Features**

Primary Product Color	Yellow
-----------------------	--------

**Mechanical Attachment**

Number of Tie-Wrap Holes	4
--------------------------	---

**Dimensions**

Tag Height	6.4 mm[.25 in]
------------	----------------

Tag Length	50.8 mm[1.8 in]
------------	-----------------

**Usage Conditions**

Operating Temperature Range	-55 – 135 °C[-67 – 221 °F]
-----------------------------	----------------------------

**Operation/Application**

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--------------------------------------------------------------

**Printer/Label Features**

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
---------------------	--------------------------------------------------------------

Printer Technology	Thermal Transfer
--------------------	------------------

**Packaging Features**



Packaging Quantity	250
--------------------	-----

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts

 <p>TE Part # 1-2186500-1 T3212-PRINTER</p>	 <p>TE Part # 1-2186502-1 T3224-PRINTER</p>	 <p>TE Part # 4-160968-1 CABLE TY 134X2.6 NAT</p>	 <p>TE Part # 2-160975-1 CABLE TY 200X4.8 NAT</p>
------------------------------------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------------------------------------	--------------------------------------------------------------------------------------------------------------------------------------------	--------------------------------------------------------------------------------------------------------------------------------------------



TE Part # 4-160968-2  
CABLE TY 134X2.6 BLACK

TE Part # 4-160971-2  
CABLE TY 140X3.6 BLACK

TE Part # 4-160975-2  
CABLE TY 200X4.8 BLA

TE Part # 2-100715-1  
CABLE TY 150X3,6NAT

TE Part # 2-100716-1  
CABLE TY 200X4,8NAT

TE Part # 2-160970-2  
CABLE TY 200X2.6 BLA

TE Part # 2-160978-1  
CABLE TY 360X4,8NAT

TE Part # 4-160970-2  
CABLE TY 200X2.6 BLA

TE Part # 4-160975-1  
CABLE TY 200X4.8 NAT

TE Part # 2-160977-2  
CABLE TY 290X4.8 BLA

TE Part # 2-160978-2  
CABLE TY 360X4,8BLA

TE Part # 2-160968-1  
FOAC CABLE TY NATURAL 134X2.6

TE Part # 1-2186501-1  
T3212-SWARE-PRINTER

TE Part # 1-2186503-1  
T3224-SWARE-PRINTER

TE Part # 2-160968-2  
CABLE TY 134X2.6 BLACK

TE Part # 2-160971-1  
CABLE TY 140X3.6 NAT

### Also in the Series | CM-SCE-TP

Printable Tags(12)

### Documents



### Product Drawings

[CM-SCE-TP-1/4-4H-4](#)

English

---

### Datasheets & Catalog Pages

[IDENTIFICATION SELECTION GUIDE](#)

English

[CM-SCE-TP Technical datasheet](#)

English

---

### Product Specifications

[Cable Markers CM-SCE, CM-SCE-TP and HL](#)

English

[CABLE MARKER INSTALLATION GUIDE](#)

English

[IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX](#)

English