

# MV-254254-10-8A ✓ ACTIVE

TE Internal #: D41400-000

Standard Labels, UL Listed, Label Width 25.4 mm [1 in], Label Height 1 in [25.4 mm], Matte Metalized Silver, Polyester, Label Thickness 86 Micron

[View on TE.com >](#)



Identification & Labeling > Labels > Standard Labels > MV Tamper Evident Polyester Labels



Label Type: **Void & Tamper Evident Labels**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent Acrylic Adhesive**

UL Listed: **Yes**

Label Width: **25.4 mm [1 in]**

[All MV Tamper Evident Polyester Labels \(22\)](#)

## Features

### Product Type Features

Label Type	Void & Tamper Evident Labels
------------	------------------------------

### Body Features

Label Color	Matte Metalized Silver
-------------	------------------------

### Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

### Printer/Label Features

Number of Labels Across	3
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	25.4 mm[1 in]
Label Height	25.4 mm[1 in]
Label Material	Polyester
Label Thickness	86 Micron

### Industry Standards

UL Listed	Yes
-----------	-----

### Packaging Features



Packaging Quantity	10000
--------------------	-------

Packaging Method	Roll
------------------	------

**Other**

Label Adhesive Type	Permanent Acrylic Adhesive
---------------------	----------------------------

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
--	--

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**





## Documents

### Product Drawings

[MV-254254-10-8A](#)

English

---

### Datasheets & Catalog Pages

[IDENTIFICATION SELECTION GUIDE](#)

English

[MV Tamper Evident Metalized Polyester](#)

English

---

### Product Specifications

[IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX](#)

English