


# STELLA

## F-056L

60" Ceiling Fan

# WAC SMART FANS



### PRODUCT DESCRIPTION

Stella offers a shining design that has something every generation can agree on. This Smart Fan fits indoor or outdoor applications - featuring three graceful blades and petite frame. Make it smart by downloading the app for additional functionality.

### FEATURES

- 6 fan speeds through both Summer and Winter Modes
- Silent DC motor
- Includes remote control with wall cradle (RC20-WT)
- Wall control for 3, 4-way control sold separately
- Compatible with WAC Smart Fans app

### AIRFLOW/ENERGY EFFICIENCY

<b>Weighted-Average/High Airflow CFM:</b>	3946/5906
<b>Weighted-Average/High Energy Use (W):</b>	20/26
<b>Estimated Yearly Energy Cost (\$):</b>	6
<b>Weighted-Average/High Efficiency (CFM/W):</b>	195
<b>Max RPM:</b>	142

### ORDER NUMBER

Model	Housing	Blade
F-056L	<b>MB</b> <i>Matte Black</i>	<b>MB</b> <i>Matte Black</i>
	<b>MW</b> <i>Matte White</i>	

### F-056L-\_\_

Example: F-056L-MB

\*This fan comes uni-pack - blade select options are not available

\* Range results may vary based on application and surroundings.

### SPECIFICATIONS

<b>Construction:</b>	Aluminum, ABS
<b>Blade:</b>	16° Pitch, 60" sweep
<b>Downrod:</b>	3/4"W X 6"H included
<b>Mounting Slope:</b>	Up to 30°
<b>Wire:</b>	80"
<b>Hanging Weight:</b>	16 lbs
<b>Total Power:</b>	39W
<b>Standards:</b>	UL/cUL Wet Location listed, Title 20 Compliant, Energy Star Rated
<b>Motor Type:</b>	DC 120 x 25 sensorless DC motor

### WIRELESS PERFORMANCE

<b>Wi-Fi Range:</b>	Up to 150 ft*
<b>Bluetooth Range:</b>	Up to 150 ft*

### LUMINAIRE PERFORMANCE

<b>Light Source:</b>	LED
<b>Light Wattage:</b>	13W
<b>Lumens/Delivered Lumens:</b>	1100/702
<b>Dimming:</b>	Integrated
<b>CRI:</b>	90
<b>Color Temperature:</b>	3000K
<b>Rated Life:</b>	50,000 hours

The WAC app synchronizes seamlessly with smart home devices you already own



wacighting.com  
Phone (800) 526.2588  
Fax (800) 526.2585

Headquarters/Eastern Distribution Center  
44 Harbor Park Drive  
Port Washington, NY 11050

Central Distribution Center  
1600 Distribution Ct  
Lithia Springs, GA 30122

Western Distribution Center  
1750 Archibald Avenue  
Ontario, CA 91760




# STELLA

F-056L

60" Ceiling Fan

**WAC**  
SMART FANS

## OPTIONAL ACCESSORIES

Bluetooth Wall Control		<b>WC20-</b>	<b>WT</b> White	Control fan speed and light brightness, and switch between Summer and Winter Modes. Additional Wall Controls can be purchased separately for multiple location control.
Bluetooth Remote Control		<b>RC20-</b>	<b>WT</b> White	Control fan speed and light brightness, and switch between Summer and Winter Modes. Compatible with WAC Smart Fans. Includes easy-to-install wall cradle and batteries.
Downrod		<b>DR12-</b> 12IN <b>DR18-</b> 18IN <b>DR24-</b> 24IN <b>DR36-</b> 36IN <b>DR48-</b> 48IN <b>DR60-</b> 60IN <b>DR72-</b> 72IN		All our downrods are 1" O.D. and are threaded on the motor end to create an extra layer of security and allow for adjustments in the field.
Downrod Couplers		<b>DC-</b>	<b>MB</b> Matte Black <b>MW</b> Matte White	Connects two downrods together.
Sloped Ceiling Kit		<b>SC-</b>		Designed to accommodate buildings with steeper sloped ceilings up to 45° or 12/12 pitch.

Examples: Wall Control - **WC20-WT**, Remote Control - **RC20-WT**, Downrod - **DR12-BN**, Downrod Coupler - **DC-MB**, Sloped Ceiling Kit - **SC-MW**

## SUGGESTED DOWNROD HEIGHT USAGE

Ceiling Height	15'	14'	13'	12'	11'	10'	9'
Downrod	72"	60"	48"	36"	24"	18"	12"

## SLOPED CEILING DEGREE CONVERSION CHART

Degree	4-8°	9-13o	14-17o	18-21o	22-25o	26-29o	30-32o	33-35o	36-38o	39-41o	42-44o	45o
Ceiling Slope	1/12	2/12	3/12	4/12	5/12	6/12	7/12	8/12	9/12	10/12	11/12	12/12
Pitch	pitch	pitch	pitch	pitch	pitch	pitch	pitch	pitch	pitch	pitch	pitch	pitch

Supplied mounting brackets allow mounting on ceiling slopes up to 30° (7/12 pitch). Optional slope kit allows mounting on ceilings up to 45° (12/12 pitch). The receiver will mount inside canopy up to 45°.

**NOTE:** Recommended maximum downrod length of 72" with 80" lead wire