

Model: 6243XXXX



FEATURES

- Energy Efficient and Long-Lasting LED Lighting
- Built-in 5.5" Dia. LED Lit Magnifier with 3x Magnification
- LED Digital Clock Display
- Smart Touch Control Switch
- Durable Aluminum Frame with Steel Back Panel
- 5mm Copper-free Mirror

LIGHTING


- LED (Light-Emitting Diode)
- Average Bulb Life of 50,000 hours
- Compatible with Most Wall Dimmers
- CRI: 85+
- Dual Color Temperature: 3000K & 6000K
- Brightness: s
- ee page 2
- Power Consumption: see page 2

SAFETY

- Safety Backed Mirror
- IP44 Rated
- UL Listed

OVERVIEW

innoci-usa does not cut corners and only uses the highest quality components and bulbs to make sure that the mirror will be maintenance free and function like the day you purchased for average 50,000 hours of use. **innoci-usa** prides itself on providing unmatched price vs quality for all of our products. All mirrors come with a 5-year limited warranty.



Model #	A	B	C	Brightness (Lumen)	Power Consumption (Watt)
62434835	48	35	1 5/8	2580	42

innoci-usa Inc.
Newport Beach, CA 92660

www.innoci-usa.com
(866) 479-8076

customerservice@innoci-usa.com

innociusa
L I F E S T Y L E