

**Model: 69354235**



### FEATURES

- Double Doors Recessed-Mount or Surface-Mount (Optional Surface-Mount Kit **Sold Separately**)
- Energy Efficient and Long-Lasting LED Lighting
- Aluminum Frame
- Double-side Mirror Door with Built-in 6" Dia. LED Lit Cosmetic Mirror
- Lighting on Both Sides of the Mirror Door
- 170° Soft-closing Hinges
- Three Adjustable Tempered Glass Shelves
- Two Color Temperatures (3000K & 6000K)
- Mirror Front Touch Switch Control
- 3-prong 120V Electrical Outlet (x2)
- USB Outlet (x2)
- Mirrored Interior
- Dimmable LED Lighting
- Copper-free Mirror

### LIGHTING


- LED (Light-Emitting Diode)
- Average Bulb Life of 50,000 hours
- Color Temperature: 3000K & 6000K
- Brightness: 9600 Lumen
- Power Consumption: 42.5 Watts

### SAFETY

- IP44 Rated

### OVERVIEW

Innoci-usa does not cut corners and only uses the highest quality components and bulbs to make sure that the mirror will be maintenance free and function like the day you purchased for average 50,000 hours of use. Innoci-usa prides itself on providing unmatched price vs quality for all of our products. All mirrors come with a 5-year limited warranty.



Innoci-USA INC  
Santa Fe Springs, CA 90670

[www.innoci-usa.com](http://www.innoci-usa.com)  
(866) 479-8076

[customerservice@innoci-usa.com](mailto:customerservice@innoci-usa.com)

**innociusa**  
LIFESTYLE

Rev. 03.5