

Crew® Restroom Floor & Surface Non-Acid Disinfectant Cleaner & Crew® Restroom Floor & Surface SC Non-Acid Disinfectant Cleaner



Non-acid restroom disinfectant cleaners that cleans, disinfects and deodorizes bathroom surfaces in one step.

Cleans and Disinfects Hard, Nonporous Surfaces

- ▶ Removes common soils without residue
- ▶ No rinsing required for non-food contact surfaces
- ▶ Provides broad spectrum efficacy against common bathroom microorganisms
- ▶ Kills HIV-1, Staphylococcus aureus, Salmonella enterica, E. coli, MRSA, VRE and other microorganisms

Effective in Hard Water

- ▶ Disinfects in up to 400 ppm hard water

Cleans and Freshens

- ▶ Deodorizes as it disinfects
- ▶ Pleasant to work with

Versatile

- ▶ Use in and out of the bathroom to clean and disinfect a variety of hard, nonporous surfaces
- ▶ Apply by mop and bucket, trigger sprayer or sponge

Designed For

- ▶ Healthcare
- ▶ Education
- ▶ Retail
- ▶ BSC
- ▶ Government
- ▶ Lodging



Use Overview

Crew® Restroom Floor & Surface Non-Acid Disinfectant Cleaner & Crew® Restroom Floor & Surface SC Non-Acid Disinfectant Cleaner are designed to provide effective cleaning, deodorizing and disinfection for hospitals, nursing homes, hotels, schools, restaurants and other institutions where housekeeping is of prime importance in controlling cross-contamination.



- ▶ For use on hard, nonporous inanimate environmental surfaces such as floors, walls, porcelain, glazed ceramic tile, plastic surfaces, shower stalls, bathtubs and cabinets.
- ▶ To disinfect inanimate, hard nonporous surfaces, dilute according to label directions.
- ▶ Apply solution with a mop, cloth, sponge or hand-pump trigger sprayer so as to wet all surfaces thoroughly.
- ▶ Allow to remain wet for 10 minutes then remove excess liquid.
- ▶ For heavily soiled areas, a pre-cleaning step is required. Prepare a fresh solution for each use.

Product Specifications

Description	Concentrate
Color/Form	Green liquid
EPA Reg. No.	1839-169-70627
Flash Point	> 200° F (> 93.4° C)
pH	6.0–8.0
Scent	Fresh
Shelf Life	1 year
Solubility	Complete

Description	Superconcentrate
Color/Form	Green liquid
EPA Reg. No.	1839-167-70627
Flash Point	130° F (54.4° C)
pH	6.5–8.0
Scent	Fresh
Shelf Life	1 year
Solubility	Complete

Available Items

Product Code	Description/Package Size	Dilution
3364707	2 x 1.5 L / 1.59 Qt. RTD® Units (Spray) - Concentrate	1:64
3063437	2 x 1.5 L / 1.59 Qt. RTD® Units (Fill) - Concentrate	1:64
04731	4 x 1 gallon / 3.78 L Containers - Concentrate	1:64
4955453	1 x 2.5 gallon / 9.45 L Envirobox™ - Concentrate	1:64
4278763	2 x 2.5 L / 84.5 oz. J-Fill® Bottles - Superconcentrate	1:256
5019211	2 x 1.4 L / 1.48 Qt. SmartDose™ Bottles - Superconcentrate	1:256 (Spray Bottle), 1:256 (Mop Bucket)
5271248	2 x 1.5 gallon / 5.67 L Command Center® Units - Superconcentrate	1:256
03905	12 x 32 oz. / 946 mL Empty Spray Bottles	

SmartDose™/MC Icons



Safety Reminder

Please make sure your employees read and understand the product label and Material Safety Data Sheet before using this product. The label contains directions for use, and both the label and MSDS contain hazard warnings, precautionary statements and first aid procedures. MSDS are available on-line at www.diversey.com or by calling 888 352 2249.

Hazard Rating

HMIS	Concentrate	NFPA	HMIS	Use Dilution 1:64	NFPA
3	Health	3	1	Health	1
0	Flammability	0	0	Flammability	0
0	Reactivity	0	0	Reactivity	0

HMIS	Superconcentrate	NFPA
3	Health	3
1	Flammability	1
0	Reactivity	0

4=Very High; 3=High; 2=Moderate; 1=Slight; 0=Insignificant.