

GFCI Receptacles	E-2
Commercial Grade Slim Series	E-3
Hospital Grade Slim Series	E-5
NAFTA Slim Series	E-6
Leaded GFCIs	E-7
Combo Pilot Light	E-7
DIN Rail	E-8
High Current	E-8
Lev-Lok®	E-9
AFCI Receptacles	E-12
GFCI Cord Sets	E-14
GFCI User Attachables	E-17
GFCI Panel Mount	E-18



GFCI RECEPTACLES

Tamper-Resistant and Non Tamper-Resistant Slim GFCI Receptacles


The SmartlockPro® Slim Series GFCIs are the latest innovation in ground fault circuit interrupter protection. Easy to install, they take up to 25% less space in the wallbox vs. typical GFCIs and can fit into any box, even shallow ones. The slim GFCIs provide all the lockout benefits of our standard SmartlockPro® offering, and are available in tamper-resistant and non-tamper-resistant versions. Constructed of resilient thermoplastic and able to withstand high torque levels, slim GFCIs come in styles for every need, including a combination guide light/receptacle and a self-test device. When it comes to smart GFCI protection, slim is certainly in.

X7599-W Shown


Takes up to 25% less space in the wallbox vs. other GFCIs



Typical GFCI



New SmartlockPro® Slim GFCI



SmartlockPro® Slim Series

Features and Benefits

- Takes up 25% less space in the wallbox vs. other tamper-resistant GFCIs
- Terminals allow for easy wiring options — back and side wire capable
- External backwire clamps provide positive visual indication of wiring and exhibit very high holding force at standard torque levels.
- Standard brass self-grounding clips (excluding WR versions)
- Patented bridge contact provides individual sets of contacts for GFCI receptacle face and downstream receptacles; no power to receptacle face if improperly wired (line-load reversed)
- Patented lockout feature for added safety prevents RESET if GFCI is not operating properly
- Dual function LED offers indication of line/load reversal and power availability
- Advanced electronics design provides superior resistance to electrical surges and over-voltages
- Trip threshold meets or exceeds UL requirements for tripping time
- Improved immunity to high frequency noise reduces nuisance tripping
- Impact-resistant thermoplastic cover and body
- TEST and RESET button colors match device face
- Compatible with all Decora® devices and wallplates; available in select Decora® colors
- NAFTA complaint versions available
- Fed Spec Rated
- Limited 2 year warranty

Tamper-Resistant

- TR symbol assures compliance with the National Electrical Code (NEC)
- Shutter mechanism inside the receptacle blocks access to the contacts unless a two-prong or three-prong plug is inserted

Self-Test

- Automatically tests the GFCI every 15 minutes and alerts users if protection has been compromised
- Two indicator lights and an audible beep signal GFCI status

Duplex Guide Light

- Sensor provides automatic ON/OFF based on ambient lighting
- Dual lens provides visible light with a variety of plugs or transformers
- Custom designed lenses with edge-mounted LEDs improve light dispersion
- Is energy-efficient, uses approx. 1W of electricity — no bulbs to replace
- Saves space by eliminating the need to use an outlet for a plug-in night light

Weather-Resistant

- Stainless steel strap and screws
- Conformally coated PC board to protect critical components from moisture
- Cold impact resistant face and buttons
- UV stabilized plastics

Hospital Grade

- Extra Heavy-Duty impact-resistant polyester cover
- Passes stringent durability test required for use in healthcare facilities including plug retention and construction integrity

GFCIs and AFCIs

TAMPER-RESISTANT AND NON TAMPER-RESISTANT RECEPTACLES, AND DEVICES





GFCI RECEPTACLES | Back and Side Wired

Continued from previous page

SmartlockPro® Slim Series Commercial Spec Grade

Back and Side Wired GFCI with Professional Grade Lockout

Rating	15A-125V @ Receptacle 20A-125V Feed-Through		20A-125V @ Receptacle 20A-125V Feed-Through		
NEMA	 5-15R		 5-20R		
Description	Color	Cat. No.		Cat. No.	
		TR	Non-TR	TR	Non-TR
GFCI with LED Indicator Light	White	X7599-W	N7599-W	X7899-W	N7899-W
(with self-grounding clip)	Ivory	X7599-I	N7599-I	X7899-I	N7899-I
	Light Almond	X7599-T	N7599-T	X7899-T	N7899-T
	Gray	X7599-GY	N7599-GY	X7899-GY	N7899-GY
	Black	X7599-E	N7599-E	X7899-E	N7899-E
	Brown	X7599	N7599	X7899	N7899
	Red	—	—	—	N7899-R
Self-Test GFCI with LED Indicator Lights	White	S7599-W	—	S7899-W	—
(with self-grounding clip)	Ivory	S7599-I	—	S7899-I	—
	Light Almond	S7599-T	—	S7899-T	—
	Gray	S7599-GY	—	S7899-GY	—
	Black	S7599-E	—	S7899-E	—
	Brown	S7599	—	S7899	—
Weather-Resistant/ Outdoor Grade GFCI with LED Indicator Light	White	WT599-W	WR599-W	WT899-W	WR899-W
	Ivory	WT599-I	—	WT899-I	—
	Light Almond	WT599-T	—	WT899-T	—
	Gray	WT599-GY	—	WT899-GY	—
	Black	WT599-E	WR599-E	WT899-E	WR899-E
Duplex GFCI with Guide Light, LED Indicator Lights	White	X7592-W	—	X7892-W	—
(with self-grounding clip)	Ivory	X7592-I	—	X7892-I	—
	Light Almond	X7592-T	—	X7892-T	—
	Black	X7592-E	—	X7892-E	—
Combination GFCI with Switch, LED Indicator Light	White	X-7299-W	—	—	—
(with self-grounding clip)	Light Almond	X-7299-T	—	—	—

TR = Tamper-Resistant.



X7899-W



WT599-W



X7592-W

Blank Face Back and Side Wired GFCI with Professional Grade Lockout

Rating	20A-125V Feed-Through Switch Rated	
Description	Color	Cat. No.
Blank Face GFCI with LED Indicator Light	White	X7590-W
(with self-grounding clip)	Ivory	X7590-I
	Light Almond	X7590-T
	Black	X7590-XE (Bulk Pack)



X7590-W

Hospital Grade SmartlockPro® Slim Series

Back and Side Wired GFCI with Professional Grade Lockout					
Rating	15A-125V @ Receptacle 20A-125V Feed-Through		20A-125V @ Receptacle 20A-125V Feed-Through		
NEMA					
Description	Color	Cat. No.		Cat. No.	
		TR	Non-TR	TR	Non-TR
GFCI Duplex Receptacle with LED Indicator Light (with self-grounding clip)	Brown	X7599-HG	N7599-HG	X7899-HG	N7899-HG
	Ivory	X7599-HGI	N7599-HGI	X7899-HGI	N7899-HGI
	White	X7599-HGW	N7599-HGW	X7899-HGW	N7899-HGW
	Black	X7599-HGE	N7599-HGE	X7899-HGE	N7899-HGE
	Gray	X7599-HGG	N7599-HGG	X7899-HGG	N7899-HGG
	Lt Almond	X7599-HGT	N7599-HGT	X7899-HGT	N7899-HGT
Self-Test GFCI Duplex Receptacle with LED Indicator Lights (with self-grounding clip)	Brown	S7599-HG	—	S7899-HG	—
	Ivory	S7599-HGI	—	S7899-HGI	—
	White	S7599-HGW	—	S7899-HGW	—
	Black	S7599-HGE	—	S7899-HGE	—
	Gray	S7599-HGG	—	S7899-HGG	—
	Lt Almond	S7599-HGT	—	S7899-HGT	—
Duplex GFCI with Guide Light, LED Indicator Light (with self-grounding clip)	Brown	X7592-HG	—	X7892-HG	—
	Ivory	X7592-HGI	—	X7892-HGI	—
	White	X7592-HGW	—	X7892-HGW	—
	Black	X7592-HGE	—	X7892-HGE	—
	Gray	X7592-HGG	—	X7892-HGG	—
	Lt Almond	X7592-HGT	—	X7892-HGT	—
Weather-Resistant Outdoor Grade GFCI Duplex Receptacle with LED Indicator Light	Brown	—	—	—	—
	Ivory	WT599-HGI	—	WT899-HGI	—
	White	WT599-HGW	—	WT899-HGW	—
	Black	—	—	—	—
	Gray	—	—	—	—
	Lt Almond	—	—	—	—
Red	—	—	—	—	



X7599-HGT



X7892-HGW



WT899-HGI

GFCI RECEPTACLES | NAFTA Compliant

SmartlockPro® Slim Series NAFTA Compliant Spec Grade Back and Side Wired GFCI with Professional Grade Lockout

NAFTA Compliant SmartlockPro® GFCIs are available for projects subject to the provisions of the North American Free Trade Agreement.

Back and Side Wired GFCI with Professional Grade Lockout

Rating	15A-125V @ Receptacle 20A-125V Feed-Through	20A-125V @ Receptacle 20A-125V Feed-Through			
NEMA	 5-15R	 5-20R			
Description	Color	Cat. No.	Cat. No.	Cat. No.	Cat. No.
		TR	Non-TR	TR	Non-TR
NAFTA Compliant Slim GFCI with LED Indicator Light (with self-grounding clip)	White Ivory	X7599-FW X7599-FI	N7599-FW N7599-FI	X7899-FW X7899-FI	N7899-FW N7899-FI
NAFTA Compliant Slim Hospital Grade Duplex GFCI with LED Indicator Light (with self-grounding clip)	Brown Ivory White Black Gray Lt Almond Red	X7599-HF X7599-HFI X7599-HFW X7599-HFE X7599-HFG X7599-HFT X7599-HFR	N7599-HF N7599-HFI N7599-HFW N7599-HFE N7599-HFG N7599-HFT N7599-HFR	X7899-HF X7899-HFI X7899-HFW X7899-HFE X7899-HFG X7899-HFT X7899-HFR	N7899-HF N7899-HFI N7899-HFW N7899-HFE N7899-HFG N7899-HFT N7899-HFR



X7899-HGR

SmartlockPro® GFCI with Professional Grade Lockout

Features and Benefits

- Patented bridge contact provides individual sets of contacts for GFCI receptacle face and downstream receptacles; no power to receptacle face if improperly wired (line-load reversal)
- Patented lockout feature for added safety prevents RESET if GFCI is not operating properly
- Advanced electronics design provides superior resistance to electrical surges and over-voltages
- Impact-resistant thermoplastic cover and body
- Expanded wiring options with eight back-wire holes (two for each line and load connection) plus ground with an internal clamp
- High-visibility power indicator illuminates when power to the receptacle is present
- Silver alloy contacts

- Compatible with all Decora® devices and wallplates; available in select Decora® colors
- Matching wallplate included
- Backed by a limited 2 year warranty



Leaded

- Include #12 AWG TEW line & load leads plus a ground wire for broadest installation flexibility
- Terminals are enclosed for added safety

Pilot Light GFCI

- Long-lasting, energy efficient LEDs with 20-year life expectancy — no bulbs to replace
- High-Visibility Power Indicator illuminates when power to the receptacle is present

SmartlockPro® Wire Lead GFCI with Professional Grade Lockout

Rating	15A-125V @ Receptacle 20A-125V Feed-Through	20A-125V @ Receptacle 20A-125V Feed-Through
NEMA	 5-15R	 5-20R
Description	Color	Cat. No.
SmartlockPro® Wire Lead Duplex GFCI	Ivory White	7599-LI 7599-LW



SmartlockPro® GFCI Receptacle with Pilot Light

Rating	15A-125V @ Receptacle 20A Feed-Through	
Description	Color	Cat. No.
SmartlockPro® GFCI Receptacle with Pilot Light	Ivory White Gray Light Almond	7591-PLI 7591-PLW 7591-PLG 7591-PLT



SmartlockPro® Heavy-Duty Spec Grade DIN-Rail

Features and Benefits

- 10kA SCCR
- GFCI receptacle is Fed Spec W-C 596 rated

Industrial Grade DIN-Rail GFCI Module

Rating	15A-125V 20A Feed-Through	20A-125V 20A Feed-Through
NEMA	 5-15R	 5-20R
Description	Color	Cat. No.
Duplex Receptacle with Indicator Light	Black	N7599-DIN N7899-DIN



N7599-DIN
DIN-Rail I

SmartLock® High-Current GFCIs Add Ground-Fault Protection to Heavy Equipment

Features and Benefits

- Contact rating at GFCI: 20-125V; load capability with 125V control relay 80A max @ 240V AC
- TEST and RESET buttons confirm proper operation
- Ideal for use with spas, heater packs, high pressure washers, industrial mixers and other equipment
- Backed by a limited 1 year warranty
- Exclusive, patented lockout-action: RESET button is blocked if GFCI protection has been compromised, eliminating the risk of end-users incorrectly assuming that a reset GFCI is providing ground fault protection when it actually is not
- Adds ground fault protection to heavy equipment powered through 3-and-4 wire circuits grounded with neutral
- Meets or exceeds UL requirements for increased surge immunity, corrosion resistance, and resistance to false tripping

SmartLock® High-Current GFCIs Add Ground-Fault Protection to Heavy Equipment

Contact Rating	Color	Cat. No.
20A/125V	Black	8895-E
20A/125V	Ivory	8895-I
20A/125V	White	8895-W




8895-W

Lev-Lok® SmartlockPro® GFCI Receptacles

Leviton's heavy duty specification grade SmartlockPro® GFCI modular receptacles are the perfect solution for those locations that require the added safety of ground fault protection, such as restrooms and kitchens. Suitable for use in all 15A or 20A, 125V commercial applications, these devices are offered in standard or tamper-resistant duplex receptacle versions. With ideal time saving benefits and excellent safety features like automatic GFCI testing after RESET and built-in end-of-life indication, Leviton's GFCI modular receptacles are the perfect choice for safety.

M7599-I Shown



GFCI RECEPTACLES | Lev-Lok® Hospital Grade

Lev-Lok® SmartlockPro® GFCI Receptacles

Features and Benefits

- GFCI protects one duplex receptacle. No feed-through capability.
- Constructed with impact-resistant nylon cover
- Large triple-wipe, brass “T” line contacts on 20A for superior contact and conductivity
- The SmartlockPro® receptacle automatically tests the GFCI every time the RESET button is pushed. The GFCI will not reset if the GFCI circuit is not functioning properly.
- Built-in end-of-life indication. If the SmartlockPro® receptacle can no longer provide GFCI protection, it will not reset and no power is supplied to the face.
- Trip threshold meets or exceeds UL requirements for tripping time
- Right Angle Wiring module’s thin profile makes it easier to place GFCI receptacle in the box
- #12 AWG THHN wire leads, 6” length on MSTWL series wiring modules
- Wiring module locks and latches to the receptacle body providing double the connection security
- Receptacle to be installed only with Leviton MSTWL series wiring modules
- MSTWL wiring module sold separately with protective label and factory-installed Circuit ID label

SmartlockPro® Hospital Grade

2-Pole, 3-Wire Grounding

Rating	15A-125V	20A-125V	
NEMA	5-15R	5-20R	
Description	Color	Cat. No.	Cat. No.
Duplex	White	M7599-HGW	M7899-HGW
	Ivory	M7599-HGI	M7899-HGI
	Light Almond	M7599-HGT	M7899-HGT
	Gray	M7599-HGY	M7899-HGY
	Black	M7599-HGE	M7899-HGE
	Brown	M7599-HG0	M7899-HG0
	Red	M7599-HGR	M7899-HGR
Duplex, Tamper Resistant	White	MT759-HGW	MT789-HGW
	Ivory	MT759-HGI	MT789-HGI
	Light Almond	MT759-HGT	MT789-HGT
	Gray	MT759-HGY	MT789-HGY
	Black	MT759-HGE	MT789-HGE
	Brown	MT759-HG0	MT789-HG0
	Red	MT759-HGR	MT789-HGR



M7599-HGI (front) with MSTWL-A Wiring Module



M7599-I (back)

GFCI RECEPTACLES | Lev-Lok® Heavy Duty Spec Grade | Wiring Modules

SmartlockPro® Heavy-Duty Spec Grade

2-Pole, 3-Wire Grounding			
Rating		15A-125V	20A-125V
NEMA		5-15R	5-20R
Description	Color	Cat. No.	Cat. No.
Duplex	White	M7599-W	M7899-W
	Ivory	M7599-I	M7899-I
	Light Almond	M7599-T	M7899-T
	Gray	M7599-GY	M7899-GY
	Black	M7599-E	M7899-E
	Brown	M7599	M7899
	Red	M7599-R	M7899-R
Duplex, Tamper Resistant	White	MT759-W	MT789-W
	Ivory	MT759-I	MT789-I
	Light Almond	MT759-T	MT789-T
	Gray	MT759-GY	MT789-GY
	Black	MT759-E	MT789-E
	Brown	MT759	MT789
	Red	MT759-R	MT789-R



MT789-W


 MSTWL-A
Wiring Module

Lev-Lok® Wiring Modules

Lev-Lok® Wiring Modules			
Device Type	Description	Color	Cat. No.
Receptacles	Stranded Wire Leads	White	MSTWL-A
	Stranded Wire Leads	Red	MSTWL-R
	Stranded Wire Leads with 4-port push wire connectors	White	MSTWL-WST
	Solid Wire Leads	White	MSTWL-SDA
	Solid Wire Leads with 4-port push wire connectors	White	MSTWL-WSD


AFCI RECEPTACLES

AFCI Receptacles

SmartlockPro® Outlet Branch Circuit AFCI Receptacles

The SmartlockPro® Outlet Branch Circuit (OBC) AFCI Receptacle offers advanced technology to help protect against electrical fires. This device is designed to interrupt power in the event potentially hazardous arcing is detected, which could originate from a number of sources including damaged wires and cords. Meeting the latest UL requirements for OBC AFCI receptacles, the device provides protection against series and parallel arcs. The SmartlockPro® OBC AFCI Receptacle features Leviton's patented reset/lockout and tamper-resistant technology. AFCI's are now required by the National Electrical Code® in many areas of the home.

AFTR1-W Shown



SmartlockPro® Outlet Branch Circuit AFCI Receptacles

Features and Benefits

- Meets or exceeds latest UL 1699A requirements for arc detection and tripping requirements on both series and parallel arcs
- Device design reduces nuisance tripping
- Impact-resistant thermoplastic cover and body
- TR symbol indicates the device's compliance with the latest NEC® requirements for tamper-resistant receptacles in residences and childcare facilities
- Superior resistance to electrical surges and over-voltages
- Expanded wiring options with nine back-wire holes (two for each line and load connection plus one for ground with an internal clamp)
- Silver alloy contacts
- Coordinates with all Decora® devices and wallplates; available in select colors
- Packed with coordinating wallplate
- Backed by a limited 2 year warranty

Lockout Action

- Automatically tests the AFCI every time the RESET button is depressed; the AFCI will not reset if the AFCI circuit is not functioning properly
- Leviton's patented reset/lockout technology prevents the AFCI from being reset in the event of a line-load reversal and stops power from being fed to the AFCI receptacle face or through to downstream devices; an illuminated green LED indicator on the AFCI's face should alert an installer to a line-load wiring reversal if the device is in the tripped state

* Upstream series arc protection is only provided where the OBC AFCI is properly wired and installed as the first outlet in the branch circuit.

SmartlockPro® Outlet Branch Circuit AFCI Receptacles

Back and Side Wired AFCI w Reset/Lockout and Tamper-Resistant Technology

Rating		15A-120V @ Receptacle 20A-125V Feed-Through	20A-120V @ Receptacle 20A-125V Feed-Through
NEMA		5-15R	5-20R
Description	Color	Cat. No.	Cat. No.
Tamper-Resistant Outlet	White	AFTR1-W	AFTR2-W
Branch Circuit AFCI	Ivory	AFTR1-I	AFTR2-I
Receptacle with	Light Almond	AFTR1-T	AFTR2-T
LED Indicator	Gray	AFTR1-GY	AFTR2-GY
	Black	AFTR1-E	AFTR2-E
	Brown	AFTR1	AFTR2



AFTR2-W

PORTABLE GFCI CORD SETS | Power Supply Cords

GFCI Cord Sets

Automatic and Manual Reset GFCI Devices

Leviton's Automatic and Manual Reset GFCI Devices are now sleeker and more rugged than ever. And, while these devices are fully OSHA compliant for use on job sites, they are also perfect for use in a variety of temporary power applications, such as recreation vehicles, marine vehicles, portable pools, portable generators, submersible pumps, vending machines and more.

GFA15-6C Shown



Automatic and Manual Reset GFCI Cord Sets and Power Supply Cords
Features and Benefits

- Rainproof, outdoor rated GFCI module
- Fully complies with NEC and OSHA regulations for construction sites
- Manual Reset Cord Sets (yellow body) will NOT automatically reset ON when power is restored after a power interruption — RESET button must be actuated
- Automatic Reset Cord Sets (black body) will automatically reset ON when plugged in or power is restored after a power interruption
- Power Indicator light goes OFF if GFCI trips, power is interrupted or GFCI is unplugged
- Open-Neutral Protection immediately trips the GFCI if the neutral conductor on the line side is opened, eliminating the possibility of the GFCI having a live hot leg
- Custom cord lengths and configurations available as special order
- Impact-resistant thermoplastic cover and body
- Water-resistant enclosure is sealed by ultrasonic welding
- Silver alloy contacts
- Fully complies with NEC and OSHA regulations for construction sites
- UL listed cord sets and user-attachables; UL recognized power supply cords; complies with UL Standard 943 as a Class A GFCI
- CSA Certified
- Backed by a limited 2 year warranty

Automatic Reset GFCI Cord Sets and Power Supply Cord Sets

Automatic Reset GFCI Cord Sets and Power Supply Cord Sets		
Rating		15A-120V
NEMA		  5-15P 5-15R
Description	Color	Cat. No.
2 ft. Cord Set, Molded, Straight Blade Plug and Connector	Black	GFA15-2C
6 ft. Cord Set, Molded, Straight Blade Plug and Connector	Black	GFA15-6C
25 ft. Cord Set, Molded, Straight Blade Plug and Connector	Black	GFA15-25C
3 ft. Cord Set, Molded, Straight Blade Plug and Triple Tap Connector	Black	GFA15-3TC
37 ft. Power Supply Cord, Molded, Straight Blade Plug, No Connector	Black	GFA15-37E
Rating		20A-120V
NEMA		  5-20P 5-20R
Description	Color	Cat. No.
3 ft. Cord Set, Molded, Straight Blade Plug and Connector	Black	GFA20-3C
37 ft. Power Supply Cord Molded, Straight Blade Plug, No Connector	Black	GFA20-37E
Rating		20A-120V
NEMA		 L5-20P
Description	Color	Cat. No.
3 ft. Cord Set, Locking Plug and Connector	Black	GFA20-3LC



GFA15-3TC



GFA20-37E

PORTABLE GFCI CORD SETS | Power Supply Cords

Manual Reset GFCI Cord Sets and Power Supply Cords

Manual Reset GFCI Cord Sets

Rating		15A-120V	
NEMA			
		5-15P	5-15R
Description	Color	Cat. No.	
3 ft. Cord Set, Molded, Straight Blade Plug and Connector**	Yellow	GFM15-3C	
25 ft. Cord Set, Molded, Straight Blade Plug and Connector	Yellow	GFM15-25C	
3 ft. Cord Set, Molded, Straight Blade Plug and Triple Tap Connector**	Yellow	GFM15-3TC	
3 1/2 ft. Cord Set, Molded, Straight Blade Plug and Connector, 14-3 SJTW Cord, one end features a 14W47 Wetguard® Plug, other end features a 15W47 Wetguard Connector	Yellow	GFM15-3WC	

**Heavy-Duty #12/3 Type SJTW Cord.



GFM20-3C

Rating		20A-120V	
NEMA			
		5-20P	5-20R
Description	Color	Cat. No.	
3 ft. Cord Set, Molded, Straight Blade Plug and Connector, 12-3 SJTW Cord	Yellow	GFM20-3C	
3 1/2 ft. Cord Set, Molded, Straight Blade, Plug and Connector, 12-3 SJTW Cord, one end features a 14W33 Wetguard Plug, other end features a 15W33 Wetguard Connector	Yellow	GFM20-3WC	

GFCI USER ATTACHABLE DEVICES

GFCI User Attachable Devices

Features and Benefits

- UL 943 Class A GFCI operation with open-neutral protection
- May be pre-wired to cable of any specified length up to 50 feet
- Accepts #18 thru #12 cord sizes Type SJ or ST
- Power indicator light goes off if GFCI trips, power is interrupted or GFCI is unplugged
- Backed by a limited 2 year warranty

16693 Shown

16694 Shown



User Attachable Devices

Right Angle GFCI Plug			
Rating		15A-120V	20A-120V
NEMA		5-15P	5-20P
Description	Color	Cat. No.	Cat. No.
Automatic Reset	Black	16693	16793
Manual Reset	Yellow	16694	16794



16693

GFCI PANEL MOUNT

GFCI Panel Mount

Features and Benefits

- Provides UL 943 Class A GFCI protection (5mA±1mA)
- A “Hi/Lo” voltage detection RED indicator lights when power supply swells or drops at approximately 160V RMS / 70V RMS (+/-10%)
- Rated 20A-120 VAC for down-stream loads; units can be easily added to equipment panels as needed
- Rugged, UV/impact-resistant polycarbonate high-visibility yellow housing, with moisture-resistant TEST and RESET buttons
- Rainproof outdoor rated GFCI module
- Automatically resets ON after power interruption
- Open-neutral protection ensures that the GFCI will trip automatically if there's a break in the neutral conductor feeding power to the GFCI
- Meets OSHA requirements for construction sites
- Backed by a limited 2 year warranty

Panel Mount GFCI with Hi/Lo Voltage Detection

Rating	20A-120V	
Description	Color	Cat. No.
Panel Mount GFCI, Rated 20A-120VAC	Yellow	46596-Y



46596-Y