

# UV-SCE-3/4-2.0-4 ✓ ACTIVE

RAYCHEM | RAYCHEM UV-SCE

TE Internal #: EC6648-000

Printable Tubing, Ladder, UV Resistant, 2:1 Shrink Ratio, Yellow, Markers per Sleeve 1, Length 2 in [50 mm], RAYCHEM UV-SCE

[View on TE.com >](#)



Identification & Labeling > Printable Tubing > UV Resistant Sleeves, UV-SCE



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **UV Resistant**

Printable Tubing Shrink Ratio: **2:1**

Primary Product Color: **Yellow**

Markers per Sleeve: **1**

[All UV Resistant Sleeves, UV-SCE \(26\)](#)

## Features

### Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	UV Resistant

### Body Features

Printable Tubing Shrink Ratio	2:1
Primary Product Color	Yellow
Markers per Sleeve	1

### Dimensions

Product Length	50 mm[2 in]
Supplied Inner Diameter	19 mm[.75 in]
Recovered Inside Diameter	9.53 mm[.375 in]
Compatible Cable Diameter Range	9.9 – 15.3 mm[.39 – .602 in]

### Usage Conditions

Operating Temperature Range	-55 – 200 °C[-67 – 392 °F]
-----------------------------	----------------------------

### Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

### Printer/Label Features



Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
---------------------	--

Printer Technology	Thermal Transfer
--------------------	------------------

### Packaging Features

Packaging Quantity	250
--------------------	-----

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
--	--

Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
-----------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



## Also in the Series | RAYCHEM UV-SCE



### Documents

#### Product Drawings

[UV-SCE-3/4-2.0-4](#)

English

#### Datasheets & Catalog Pages

[UV-SCE](#)

English

#### Product Specifications

[UV-SCE](#)

English

[IDENTIFICATION PRINTER PRODUCT RIBBON MATRIX](#)

English

#### Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

