

# Classic Plus 26

MOVINCOOL®  
THE #1 SPOT COOLING SOLUTION

The MovinCool Classic Plus 26 portable air conditioner has all the benefits of our proven Classic Series, PLUS new features designed to increase performance and control. The versatile Classic Plus is instantly ready to provide cool air in the hottest environments such as production lines, outdoor events, manufacturing processes, injection molding, metal forming and much more.

The Classic Plus features a programmable digital temperature controller allowing the user to "set" the desired temperature. By cooling only the area that needs it, the Classic Plus 26 portable air conditioner saves you money while protecting people and equipment and speeding up processes. Self-contained and portable, the Classic Plus 26 requires little or no installation—simply roll it in, plug it in and turn it on.

- Programmable digital temperature control, set the desired temperature and walk away
- Totally self-contained with no costly installation necessary
- Handles temperatures up to 113°F, provides cooling in the hottest environments
- Provides up to 24,000 Btu/h of cool air, maximum cooling to just the spot that needs it



# MOVINCOOL®

THE #1 SPOT COOLING SOLUTION

800.264.9573  
www.movincool.com

DENSO SALES CALIFORNIA, Inc. 3900 Via Oro Ave. Long Beach, CA 90810



TECHNICAL SPECS		CLASSIC PLUS 26*
Electronic Features	Control	Programmable
Cooling Capacity	Rating Conditions: 95°F at 60% RH	24,000 Btu/h
Electrical Characteristics	Voltage Requirements Total Power Consumption Current Consumption Recommended Fuse Size NEMA Plug Configuration Min. – Max. Voltage	1 Phase, 208/230V 3.1 kW 14.0 amps 20 amps 6 - 20 198 - 250
Fans	Motor Output - high/low	0.55/0.38 kW
Evaporator	Fan Type Max. Air Flow - high/low Max. External Static Pressure	Centrifugal 708/600 CFM 0.54 IWG
Condenser	Fan Type Max. Air Flow - high/low Max. External Static Pressure	Centrifugal 1680/1460 CFM 0.25 IWG
Compressor	Type Output	Hermetic Scroll 1.5 kW
Refrigerant	Type	R-410A
Dimensions	W x D x H	19 x 29 x 47 in
Net Weight/Shipping Weight		235/265 lb
Power Cord	Gauge/Length	12 AWG (3-core)/6 ft
Condensate Tank Capacity		5 gal
Operating Conditions	Min. – Max. (@ 50% RH)	70° - 113°F
Max. Equivalent Duct Length	Per Cold Duct Hose Hot Duct Hose	60 ft 45 ft
Max. Sound Level	With Condenser - Duct high/low Without Condenser - Duct high/low	66/64 dB(A) 69/67 dB(A)

\* Specification information shown with 230V

All specifications subject to change without notice.

© 2013 DENSO SALES CALIFORNIA, INC. MovinCool, SpotCool and Office Pro are registered trademarks of DENSO Corporation.

360-0213-CP26

