

# Compact Filter Silencers

## FS Series 1/2" - 6" MPT, Flange




### Features

- Fully drawn weatherhood - no welds to rust or vibrate apart
- Tubular silencing design - tubes are positioned to maximize attenuation and air flow while minimizing pressure drop
- Durable carbon steel construction with baked enamel finish & powder coated weatherhood

### Technical Specifications

- Temp (continuous): min -15°F (-26°C) max 220°F (104°C)
- Filter change out differential: 15-20" H<sub>2</sub>O over initial Δ P
- Pressure drop graphs available upon request
- Polyester: 99%+ removal efficiency standard to 5 micron
- Paper: 99%+ removal efficiency standard to 2 micron



### Options

- 1/8" tap holes available for 3" and larger connections
- Pressure drop indicator (See page 3-11)
- Various media for different environments
- Stainless steel construction
- Epoxy coated finish
- Special connections
- Side Access Silencer Filters (LQB Series) for space restricted enclosures (select models)

*Tidbit:* Charlie Solberg Sr. "Senior" designed our first filter silencer in 1966. The FS-15 size filter was created for small air compressors.

### Outlet Connections

MPT Outlet	Assembly SCFM Rating	Assembly Part Number		Dimensions - inches			No. of Silencing Tubes	Approx. Wt. lbs	Replacement Element Part No.		Element SCFM Rating
		Polyester	Paper	A	B	C			Polyester	Paper	
1/2"	10	FS-15-050	FS-14-050	4	1 1/2	6	1	2	15	14	35
3/4"	25	FS-15-075	FS-14-075	4	1 1/2	6	2	2	15	14	35
1"	35	FS-15-100	FS-14-100	4	1 1/2	6	3	2	15	14	35
1"	55	FS-19P-100	FS-18P-100	6 5/8	1 5/8	6	3	3	19P	18P	100
1 1/4"	70	FS-19P-125	FS-18P-125	6 5/8	1 5/8	6	5	3	19P	18P	100
1 1/2"	85	FS-19P-150	FS-18P-150	6 5/8	1 5/8	6	5	4	19P	18P	100
2"	135	FS-31P-200	FS-30P-200	7 1/4	2 1/4	10	5	8	31P	30P	195
2"	135	FS-231P-200	FS-230P-200	12 1/4	2 1/4	10	5	14	231P	230P	300
2 1/2"	195	FS-31P-250	FS-30P-250	7 1/2	2 1/2	10	5	8	31P	31P	195
2 1/2"	195	FS-231P-250	FS-230P-250	12 1/2	2 1/2	10	9	15	231P	230P	300
3"	300	FS-231P-300	FS-230P-300	13	3	10	9	15	231P	230P	300
3"	300	FS-235P-300	FS-234P-300	13	3	16	9	29	235P	234P	570
3"	300	FS-275P-300	FS-274P-300	13	3	16	9	33	275P	274P	1100
4"	520	FS-235P-400	FS-234P-400	14	4	16	9	30	235P	234P	570
4"	520	FS-275P-400	FS-274P-400	14	4	16	9	34	275P	274P	1100
5"	800	FS-245P-500	FS-244P-500	14	4	16	14	33	245P	244P	880
5"	800	FS-275P-500	FS-274P-500	14	4	16	14	36	275P	274P	1100
6"	1100	FS-275P-600	FS-274P-600	15	5	16	18	38	275P	274P	1100

See Filter Silencer Technical Data section for sizing guidelines.

Dimension tolerance  $\pm 1/4"$


### Flange Outlet Connections

Flange Outlet	Assembly SCFM Rating	Assembly Part Number		Dimensions - inches			No. of Silencing Tubes	Approx. Wt. lbs	Replacement Element Part No.		Element SCFM Rating
		Polyester	Paper	A	B	C			Polyester	Paper	
4"	520	FS-235P-400F	FS-234P-400F	14	4	16	9	33	235P	234P	570
4"	520	FS-275P-400F	FS-274P-400F	14	4	16	9	39	275P	274P	1100
5"	800	FS-245P-500F	FS-244P-500F	14	4	16	14	38	245P	244P	880
5"	800	FS-275P-500F	FS-274P-500F	14	4	16	14	41	275P	274P	1100
6"	1100	FS-275P-600F	FS-274P-600F	15	5	16	18	42	275P	274P	1100

See Filter Silencer Technical Data section for sizing guidelines.

Dimension tolerance  $\pm 1/4"$

125/150# Pattern Flg	Dimensions - inches			No. of Holes	Flange Thickness
	O.D.	B.C.	B.H.		
4"	9	7 1/2	0.75	8	0.38
5"	10	8 1/2	0.88	8	0.38
6"	11	9 1/2	0.88	8	0.38



Note: Model offerings and design parameters may change without notice. See [www.solbergmfg.com](http://www.solbergmfg.com) for most current offering.